



360G2 Cassette 6 SC Angled Singlemode Green with Pigtails A

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette with pigtails
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	G.652.D and G.657.A1 , TeraSPEED®   OS2
<b>Total Fibers, quantity</b>	6

## Dimensions

<b>Depth</b>	119.38 mm   4.70 in
<b>Height</b>	30.48 mm   1.20 in
<b>Pigtail Length</b>	1.5 m   4.9 ft
<b>Width</b>	91.44 mm   3.60 in

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## General Specifications

<b>Interface, front</b>	SC
<b>Adapter Color</b>	Green
<b>Interface Feature, front</b>	Standard
<b>Package Quantity</b>	1
<b>Total Ports, quantity, front</b>	6

## Optical Performance

<b>Insertion Loss, typical</b>	0.40 dB
<b>Return Loss, minimum</b>	65.0 dB

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system



## Included Products

- 860312875 (Product Component—not orderable) — TeraSPEED® SC APC 0.9 mm Pigtail, blue, 1.5 m
- 760095596 | X-TB-8W-BL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 760211201 | X-TB-8G-BL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860312883 (Product Component—not orderable) — TeraSPEED® SC APC 0.9 mm Pigtail, orange, 1.5 m
- 760095604 | X-TB-8W-OR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
  - 760211219 | X-TB-8G-OR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860312891 (Product Component—not orderable) — TeraSPEED® SC APC 0.9 mm Pigtail, green, 1.5 m
- 760095612 | X-TB-8W-GR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860312909 (Product Component—not orderable) — TeraSPEED® SC APC 0.9 mm Pigtail, brown, 1.5 m
- 760095620 | X-TB-8W-BR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860312917 (Product Component—not orderable) — TeraSPEED® SC APC 0.9 mm Pigtail, slate, 1.5 m
- 760095638 | X-TB-8W-SL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860312925 (Product Component—not orderable) — TeraSPEED® SC APC 0.9 mm Pigtail, white, 1.5 m
- 760095646 | X-TB-8W-WH-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 760061374 | AFA-SC06-GR-SHUTTERED — TeraSPEED® SC-APC Multiport Shuttered Adapter, Green, Single Pack