


## ReadyPATCH® Multimode OM1 Keyed Module, 12 LC ports, brown



- Part of the Uniprise® ReadyPATCH® Pre-terminated Fiber line

### **OBSOLETE**

**This product was discontinued on: March 1, 2018**

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	OptiSPEED®   ReadyPATCH®
<b>Product Type</b>	Fiber module
<b>Regional Availability</b>	North America

## Construction Materials

<b>Fiber Type</b>	OM1
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Depth</b>	127.00 mm   5.00 in
<b>Height</b>	27.94 mm   1.10 in
<b>Width</b>	129.54 mm   5.10 in

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

## General Specifications

<b>Interface, front</b>	LC
<b>Total Ports, quantity, front</b>	12
<b>Interface Feature, front</b>	Keyed
<b>Color, front</b>	Brown
<b>Adapters, quantity, front</b>	6
<b>Shuttered</b>	Yes
<b>Interface, rear</b>	MPO Male
<b>Adapters, quantity, rear</b>	1
<b>Interface Feature, rear</b>	Standard

**Color, rear** Gray  
**Package Quantity** 1

## Optical Performance

**Insertion Loss, maximum** 0.90 dB

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

460117450 (Product Component—not orderable) — LazrSPEED® LC Duplex Hybrid Keyed Adapter, Brown

## LazrSPEED® LC Duplex Hybrid Keyed Adapter, Brown

### Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	LazrSPEED®
<b>Product Type</b>	Fiber adapter
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### Construction Materials

<b>Alignment Sleeve Material</b>	Zirconia
<b>Fiber Mode</b>	Multimode   Singlemode

### General Specifications

<b>Interface</b>	LC
<b>Body Style</b>	Duplex
<b>Interface Feature</b>	Keyed
<b>Color</b>	Brown
<b>Package Quantity</b>	1
<b>Shuttered</b>	No
<b>Total Ports, quantity</b>	2
<b>Transmission Standards</b>	TIA/EIA-568-B.3   TIA/EIA-604 FOCIS-3

### Mechanical Specifications

<b>Mount Type</b>	No flange
-------------------	-----------

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

