FL1-H38888N2-1210N



FL1000 Fiber Wall Box, 2-door, singlemode LC/UPC, 48-ports, with pigtails and splice tray, 1 cable clamp, 2 compression fittings, 1 grounding kit

- Ideal for small to medium fiber counts within communication rooms or closets at customer sites
- Provides demarcation access for the telecom carrier and the end-user by way of separate compartments
- Guarantees mechanical protection and fiber management for indoor and outdoor cable
- Fully customizable for patch-patch, splice-patch or for the storage of un-terminated (dark) fibers

Product Classification

Regional Availability	North America	
Product Type	Fiber wall box	
Product Series	FL1000	
General Specifications		
Application	Patching Splicing	
Adapter Packs Included, quantity	4	
Adapters, quantity	48	
Cable Clamps, quantity	1	
Cable Compression Fittings, quantity	2	
Cable Entry Location	Bottom left Bottom right Top left Top right	
Cable Type	Pigtails - Stranded	
Color	Putty white	
Door, quantity	2	
Front Door Type	Single hinged	
Growth Configuration	Fully loaded	
Interface	LC/UPC	
Mounting	Wall	
Splicing Type	Heat shrink, mass fusion	
Total Fibers, quantity	48	
Total Ports, quantity	48	

Dimensions

Page 1 of 3


©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023



FL1-H38888N2-1210N

Height	590 mm 23.228 in
Width	551 mm 21.693 in
Depth	156.97 mm 6.18 in

Outline Drawing



Material Specifications	
Finish	Powder coated
Material Type	Steel
Optical Specifications	
Fiber Mode	Singlemode
Environmental Specifications	
Environmental Space	Indoor
Qualification Standards	NEMA type 12
Packaging and Weights	
Included	One grounding kit

Packaging quantity

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023

1



FL1-H38888N2-1210N

Packaging Type

Bag | Carton

Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023

