

# 760036457 | MODG2-6SCA-SM-PT-B

G2 Modular Cassette with 6 SC APC TeraSPEED® Singlemode Pigtails, Type B

## OBSOLETE

### Replaced By:

760109587

360G2 Cartridge 6-SCA-SM-GR-PIGTAILS B

360G2 Singlemode Fiber Cassette 6 SC APC with pigtails B

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | SYSTIMAX®   |
| <b>Product Type</b>          | Fiber cassette with pigtails  |
| <b>Product Brand</b>         | TeraSPEED®  |

## General Specifications

|                                     |                  |
|-------------------------------------|------------------|
| <b>Adapter Color</b>                | Green            |
| <b>Interface, front</b>             | SC/APC           |
| <b>Interface, rear</b>              | Stranded pigtail |
| <b>Total Fibers, quantity</b>       | 6                |
| <b>Total Ports, quantity, front</b> | 6                |

## Dimensions

|                       |                    |
|-----------------------|--------------------|
| <b>Height</b>         | 30.48 mm   1.2 in  |
| <b>Width</b>          | 91.44 mm   3.6 in  |
| <b>Depth</b>          | 119.38 mm   4.7 in |
| <b>Pigtail Length</b> | 1.5 m   4.921 ft   |

## Optical Specifications

|                                |  |
|--------------------------------|--|
| <b>Fiber Type</b>              | G.652.D and G.657.A1, TeraSPEED®   OS2 |
| <b>Insertion Loss, typical</b> | 0.4 dB                                 |
| <b>Return Loss, minimum</b>    | 65 dB                                  |

## Environmental Specifications

# 760036457 | MODG2-6SCA-SM-PT-B

---

**Safety Standard** UL

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system



## Included Products

- 760061374 AFA-SC06-GR-SHUTTERED – TeraSPEED® SC-APC Multiport Shuttered Adapter, Green, Single Pack
- 860312933 – TeraSPEED® SC APC 0.9 mm Pigtail, red, 1.5 m
- 860312941 – TeraSPEED® SC APC 0.9 mm Pigtail, black, 1.5 m
- 860312958 – TeraSPEED® SC APC 0.9 mm Pigtail, yellow, 1.5 m
- 860312966 – TeraSPEED® SC APC 0.9 mm Pigtail, violet, 1.5 m
- 860312974 – TeraSPEED® SC APC 0.9 mm Pigtail, rose, 1.5 m
- 860312982 – TeraSPEED® SC APC 0.9 mm Pigtail, aqua, 1.5 m