

760053207 | KIT-CLEANING



Cleaning Consumables Kit, Fiber Optic

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cleaning and inspection kit

General Specifications

Compatible Interface	LC MPO SC ST
-----------------------------	--------------------

Packaging and Weights

Included	(2x) Forty cleaning swabs, 1.25 mm (2x) Forty cleaning swabs, 2.5 mm Fiber cleaning solution, 3 oz Instruction sheet LC I.B.C. MTP/MPO I.B.C Reel cleaner refill (six per pack) SC I.B.C.
-----------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- 1918806-1 - Reel cleaner refill (six per pack)
- 1918809-1 - Fiber Optic MTP/MPO IBC (In Bulkhead Cleaner)
- 2064499-1 - Fiber Optic SC IBC (In Bulkhead Cleaner)
- 2064500-1 - Fiber Optic LC IBC (In Bulkhead Cleaner)

1918806-1



Reel cleaner refill (six per pack)

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cleaning kit

General Specifications

Color	Blue
Compatible Connector Type	FC LC MPO (female) MT-RJ (female) SC ST

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Packaging quantity	6
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant





Fiber Optic MTP/MPO IBC (In Bulkhead Cleaner)

- Cleans male or female MTP/MPO connectors
- Handles more than 400 cleanings per cleaner

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cleaning kit

General Specifications

Color Blue

Dimensions

Height	56.5 mm 2.224 in
Width	22 mm 0.866 in
Length	184.2 mm 7.252 in

Environmental Specifications

Environmental Space Indoor

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant





Fiber Optic SC IBC (In Bulkhead Cleaner)

- Simple pushing motion to engage tool
- Audible CLICK to alert the operator when tools is fully engaged
- Dry cleaning strand eliminates the need for solvents to be effective
- Over 525+ engagements per unit

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cleaning kit

General Specifications

Color	Blue
Interface	SC

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



2064500-1



Fiber Optic LC IBC (In Bulkhead Cleaner)

Product Classification

Regional Availability	Australia/New Zealand Latin America North America
Portfolio	NETCONNECT®
Product Type	Fiber cleaning kit

General Specifications

Color	Blue
Interface	LC

Dimensions

Height	17.5 mm 0.689 in
Width	17.5 mm 0.689 in
Length	181 mm 7.126 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

