CS-B-A



Cluster Support Bracket with angle member attachment

Product Classification

Support bracket

General Specifications


Cable Runs, quantity	7
Hole, quantity	7
Mounting	Cluster support
Dimensions	
Height	127 mm 5 in
Width	228.6 mm 9 in
Length	152.4 mm 6 in
Pipe Outer Diameter	60.96 mm 2.4 in
Hole Size	3/4 in 7/16 in

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 19, 2023



Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included

Packaging quantity 1

Weight, net 1.8 kg | 3.968 lb

Regulatory Compliance/Certifications

Agency

Classification

Brackets

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: January 19, 2023



CS-B-A

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



Included Products

ACS-12	-	Antenna and RRU Cable Support Bracket for up to 12 Cables
CS-B	-	Cluster Support Bracket
PG-CS08	-	PIM-Guard Antenna and RRU Cable Support Bracket with 8 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements.For patents, see www.cs-pat.com
PG-CS23	-	PIM-Guard Antenna and RRU Cable Support Bracket with 23 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat.com
PG-CSEB17	-	PIM-Guard Expansion Bracket - expands PG-CS08 Cable Support Bracket to 23 Ports. For patents, see www.cs-pat.com
PG-RM06	_	PIM-Guard Round Member Cable Support Bracket 6 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 5 to 7 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat.com
PG-RMBH12	-	PIM-Guard Round Member Cable Support Bracket for Block Hangers - Two 3/8" stainless steel threaded rods for up to 12 hangers. Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements.
PG-RMBH12-BP	_	PIM-Guard Round Member Cable Support Bracket for Block Hangers (pkg of10)- Two 3/8" stainless steel threaded rods for up to 12 hangers. Install with torque wrench set at 10 to 15 ft- Ib to meet carrier PIM requirements.

Page 3 of 3

