

# SSC-760233122X6 | 18 in Pole Top for C-Band Radios and 4G Antenna



## Top of Pole 18in Dia Concealment Enclosure for C-Band and power supply

- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your CommScope Representative for exact model number.

Mounts directly to CommScope poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

Supports Ericsson C-Band 8863 with 6302 power supply

Coming support of 4415/4426/4478 with additional kit

Supports Samsung RT8808 and Delta 2.0 or ABB power supply

-Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Pole top
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, CommScope</b>	CommScope Canister Antennas
<b>Antenna Compatibility, Other Vendors</b>	ACE   AMPHENOL   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)
<b>Cooling</b>	Passive Cooling
<b>Mounting Options</b>	Concrete poles   Fluted poles   Metal poles   Non-tapered poles   Tapered poles   Wood poles
<b>Power Supply Compatibility</b>	6302   ABB CC1600   DELTA 2.0   PSU-AC-08

# SSC-760233122X6 | 18 in Pole Top for C-Band Radios and 4G Antenna

---

**Radio Compatibility, Ericsson** 4415 | 4426 | 4478 | 8863

**Radio Compatibility Samsung** RT8808-77A

**Radios Included** None

## Dimensions

**Height** 812.8 mm | 32 in

**Width** 457.2 mm | 18 in

**Depth** 457.2 mm | 18 in

**Mounting Bolt Circle Diameter** 142.748 mm | 5.62 in | 241.3 mm | 9.5 in

## Material Specifications

**Finish Aluminum** Chromate

**Finish Concealment Covers** Powder coated

**Material Type** Aluminum | Steel

## Environmental Specifications

**Thermal Compliance** GR-487

## Packaging and Weights

**Volume** 0.134 m<sup>3</sup> | 4.72 ft<sup>3</sup>

**Weight (unloaded)** 34.019 kg | 75 lb

## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines