REVISIONS 1.0 GENERAL NOTES 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X. X] REV. DESCRIPTION BY DATE 1.2 FOR PATENT INFO: https://www.cs-pat.com ACG Α INITIAL RELEASE TP 2.0 DESIGN NOTES 14JAN06 2.1 ANY HAZARDS OR OBSTRUCTIONS TO THE CLIMBING FACILITY AND SAFETY CLIMB MUST BE ACG 11DEC08 В ΤP REPLACE J-BOLT FROM JB-HK IDENTIFIED PRIOR TO INSTALLING THE APPURTENANCE. ADDITIONAL PRODUCTS MAY BE REQUIRED TO MAINTAIN THE INTEGRITY OF THE SAFETY CLIMB. DURING INSTALLATION, MSM С **UPDATE BOM** TP 16MAY13 TEMPORARY AND/OR PERMANENT PRECAUTIONARY MEASURES SHOULD BE TAKEN TO D PRESERVE THE CLIMBING FACILITY AND/OR SAFETY CLIMB. LS1146 **BCROSS** D **UPDATED TEMPLATES & ADDED SHEE1** 15MAY23 40171416CMO 3.0 MANUFACTURING/SPECIAL REQUIREMENTS 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT. 4.0 TEST 5.0 PACKAGING 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005 5.1 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER 5.1 EXTRA HARDWARE MAYBE SUPPLIED, BAGGED AND SHIPPED DETAIL A SCALE 1:3 ANGLE MEMBER **SET-UP** COMMSCOPE, INC. OF NORTH CAROLINA **ROUND MEMBER** DETAIL B SCALE 1:3 SET-UP SAP MATERIAL MASTER 0 PLACE $.x[.x] \pm 0.12[3.0]$ 2 PLACE $.xxx[.x] \pm 0.030[0.8]$ CL-0610-U 1 PLACE $.XX[.X] \pm 0.06[1.5]$ **ANGLES** MATERIAL COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES; INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT. NOTE NO. QTY. ITEM PART NO. DESCRIPTION WEIGHT DATE UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994 CL10.01 10' ANGLE SIDE RAIL 16.37 LBS 2 CABLE LADDER, 10', 6 HOLE, UNIV. HDWR Α 2 CL06R.01 20" LADDER RUNG 1.69 LBS 3 DENSITY 3 HKCLU.02 BACKING PLATE 4 0.95 LBS MASS | 43.63 GB-03145 10 0.065 LBS 4 3/8" X 1-1/2" GALV BOLT KIT SCALE DOCUMENT NO. VOLUME 154.80 05/19/2023 1:12 CL-0610-U 8" GALV J-BOLT KIT 5 GJB0380 0.23 LBS 4 SURFACE AREA 2465.63 ECN 40171416CMO 6 GWF-03 3/8" GALV FLAT WASHER 8 0.01 LBS HEIGHT | 123.9" INSL DRAWING SIZE Auth Group MODEL SHEET GWL-03 3/8" GALV LOCK WASHER 0.01 LBS 7 4 VERSION STATUS REVISION LENGTH 23.7" VERSION STATUS REVISION © 2023 CommScope, Inc. Confidential 1 OF 2 0.02 LBS 3/8" GALV HEX NUT GN-03 4 WIDTH 8.3" RE RE D 2

