


SSC-760236577N2 | 18 in Pole Top for Nokia or Samsung



Top of Pole 18in Dia Concealment Enclosure for up to three Nokia Metro Cell radios Or Samsung LAA/CBRS

- Enclosure for holding up to 3 Nokia metro cell radios directly below a multiband canister antenna
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your ANDREW Representative for exact model number.

-Supports AWHQN with separately available kit "860665079-AMK-001"

-Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket
- 860664823-AMK-004 PT18 Nokia to Ericsson Retrofit Kit

Mounts directly to ANDREW poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

Product Classification

Product Type	Pole top
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, ANDREW	ANDREW Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver White (RAL 9010)
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Radio Compatibility, Nokia	(3) Airscale micro radios (Including LAA & CBRS models) AHFB AHIA AHIB AWHQN AZRB Airscale micro Diplexer Power Distribution
Radio Compatibility Samsung	Diplexer Power Distribution RT2201-46A RT4401-48A

SSC-760236577N2 | 18 in Pole Top for Nokia or Samsung

Radios Included	None
Dimensions	
Height	812.8 mm 32 in
Width	457.2 mm 18 in
Depth	457.2 mm 18 in
Mounting Bolt Circle Diameter	142.748 mm 5.62 in 241.3 mm 9.5 in

Material Specifications

Finish Aluminum	Chromate
Finish Concealment Covers	Powder coated
Material Type	Aluminum Steel

Environmental Specifications

Thermal Compliance	GR-487
---------------------------	--------

Packaging and Weights

Volume	0.134 m ³ 4.72 ft ³
Weight (unloaded)	34.019 kg 75 lb