

FDT-AJ012NXT2500



iFDT Indoor Fiber Distribution Terminal, 12-fiber, SC/APC, loose tube OSP cable, 2500 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Series	IFDT

General Specifications


Adapters, quantity	12
Cable Entry Location	Bottom right Top right
Cable Type	OSP - Loose Tube
Color	Putty white
Front Door Type	Double hinged
Growth Configuration	Fully loaded
Interface	SC/APC
Interface, stub	No connector
Lock Type	Padlock ready
Mounting	Wall
Port, quantity	12

Dimensions

Height	184.15 mm 7.25 in
Width	299.72 mm 11.8 in
Depth	82.55 mm 3.25 in
Cable Length	762 m 2500 ft

Ordering Tree

FDT-AJ012NXT2500



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity 1

FDT-AJ012NXT2500

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

