



EW127A, HELIAX® Standard Elliptical Waveguide, 11.7–13.25 GHz, black non-halogenated, fire retardant polyolefin jacket

## Product Classification

<b>Brand</b>	HELIAX®
<b>Product Type</b>	Elliptical waveguide

## Construction Materials

<b>Jacket Material</b>	Non-halogenated, fire retardant polyolefin
<b>Conductor Material</b>	Corrugated copper
<b>Jacket Color</b>	Black

## Dimensions

<b>Cable Volume</b>	251.0 L/km   2.7 ft <sup>3</sup> /kft
<b>Cable Weight</b>	0.43 kg/m   0.29 lb/ft
<b>Diameter Over Jacket (E Plane)</b>	28.20 mm   1.11 in
<b>Diameter Over Jacket (H Plane)</b>	17.10 mm   0.67 in

## Electrical Specifications

<b>Operating Frequency Band</b>	11.7 – 13.25 GHz
<b>eTE11 Mode Cutoff</b>	7.670 GHz
<b>Group Delay</b>	128 ns/100 ft @ 12.700 GHz 419 ns/100 m @ 12.700 GHz

## Environmental Specifications

<b>Installation Temperature</b>	-25 °C to +60 °C (-13 °F to +140 °F)
<b>Operating Temperature</b>	-30 °C to +80 °C (-22 °F to +176 °F)
<b>Storage Temperature</b>	-30 °C to +80 °C (-22 °F to +176 °F)

## Mechanical Specifications

<b>Fire Retardancy Test Method</b>	UL 1666/CATVR/CMR
<b>Maximum Twist</b>	6.00 °/m   2.00 °/ft
<b>Minimum Bend Radius, Multiple Bends (E Plane)</b>	150.00 mm   6.00 in
<b>Minimum Bend Radius, Multiple Bends (H Plane)</b>	380.00 mm   15.00 in
<b>Minimum Bend Radius, Single Bend (E Plane)</b>	130.00 mm   5.00 in
<b>Minimum Bend Radius, Single Bend (H Plane)</b>	280.00 mm   11.00 in
<b>Toxicity Index Test Method</b>	IEC 60754-2

## Note

**Performance Note** Values typical, unless otherwise stated

## Standard Conditions

<b>Attenuation, Ambient Temperature</b>	24 °C   75 °F
<b>Average Power, Ambient Temperature</b>	40 °C   104 °F
<b>Average Power, Temperature Rise</b>	42 °C   76 °F

## Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
11.7–13.25 GHz	1.15	23.10

\* VSWR/Return Loss indicated is for lengths up to 300 ft (91.4 m)

\* VSWR/Return Loss is guaranteed for factory-fit and typical for field-fit assemblies

\* Custom length performance: Call 828-324-2200 or 1-800-982-1708 (toll free), or your local CommScope representative

## Attenuation

Frequency (GHz)	Attenuation (dB/100 ft)	Attenuation (dB/100 m)	Average Power (kW)	Group Velocity %
11.7	3.742	12.276	1.196	75.5
12	3.684	12.086	1.214	76.7
12.2	3.633	11.918	1.232	77.8
12.4	3.587	11.769	1.247	78.8
12.7	3.546	11.634	1.262	79.7
13	3.509	11.514	1.275	80.6
13.2	3.476	11.405	1.287	81.4

## Regulatory Compliance/Certifications

Agency	Classification
UL/ETL Certification	CATVR/CMR
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Below Maximum Concentration Value (MCV)

