

CMAX-DM60-43-V53



Cell-Max™ Low PIM Directional High Capacity Venue MIMO Antenna, 698–960 MHz and 1710–2700 MHz, 60°, 8.0 dBi

Electrical Specifications

Frequency Band, MHz	698–800	800–960	1695–1880	1850–1990	1920–2180	2200–2700	2300–2360
Gain, dBi	8.6	9.2	9.3	9.1	9.3	9.7	9.4
Beamwidth, Horizontal, degrees	60	59	55	54	56	59	61
Beamwidth, Vertical, degrees	61.0	58.0	56.0	58.0	58.0	57.0	59.0
Front-to-Back Total Power at 180° ± 30°, dB	24	26	24	26	28	26	28
CPR at Boresight, dB	24	24	20	20	20	20	20
Isolation, Cross Polarization, dB	30	30	30	30	30	30	30
VSWR Return Loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-153	-153	-153
Input Power per Port, maximum, watts	200	200	200	200	200	200	200
Polarization	±45°	±45°	±45°	±45°	±45°	±45°	±45°
Impedance	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm

Product Classification

Brand	Cell-Max™
Product Type	Indoor/outdoor antenna

General Specifications

Antenna Type	Directional
Application	Indoor Outdoor
Includes	Mounting bracket
Number of Ports, all types	2
Package Quantity	1

Mechanical Specifications

Color	White
Radome Material	ABS, UV resistant
RF Connector Interface	4.3-10 Female
Wind Loading, maximum	294.0 N @ 216 km/h

CMAX-DM60-43-V53

Wind Speed, maximum 66.1 lbf @ 216 km/h
216 km/h | 134 mph

Environmental Specifications

Ingress Protection Test Method IEC 60529:2001, IP65
Operating Temperature -40 °C to +60 °C (-40 °F to +140 °F)
Relative Humidity Up to 100%
Vibration Test Method ASTM D4169 | IEC 60068-2-6


Dimensions

Depth 124.5 mm | 4.9 in
Length 299.7 mm | 11.8 in
Width 299.7 mm | 11.8 in
Net Weight 2.9 kg | 6.4 lb

Packed Dimensions

Depth 230.0 mm | 9.1 in
Length 520.0 mm | 20.5 in
Width 350.0 mm | 13.8 in
Shipping Weight 7.3 kg | 16.1 lb

Outline Drawing



Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification

