



Fiber Optic Entrance Cabinet, 288 stranded fibers, 864 ribbon fibers, single standard drawer

- Provides splicing, administration and storage for outside plant (OSP) and intrafacility cables (IFC)
- Offers a cost-effective, space-saving alternative to splicing on the fiber frame
- Cabinets are designed for deployment in a building equipment area
- Bend radius protection and discrete subunit routing paths ensure easy installation
- Can deploy high count of stranded or ribbon fiber cables

This product will be discontinued on: July 31, 2019

Replaced By

FEC-12

Fiber Optic Entrance Cabinet, 12 Drawers, Wall mounted

Product Classification

Product Series	FEC
Product Type	Fiber entrance cabinet
Regional Availability	Australia/New Zealand Latin America North America

Dimensions

Depth	330.00 mm 12.99 in
Height	711.00 mm 27.99 in
Width	813.00 mm 32.01 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

General Specifications

Color	Putty white
Includes	Grommets
Splice Drawers, quantity	12
Splice Trays Included, quantity	0
Splicing Capacity Note	up to 288 stranded fibers or 864 ribbon fibers
Splicing Capacity, maximum	864

Mechanical Specifications

Access	Front
Cable Entry Location	Bottom Top
Cable Exit Location	Side

Mount Type

Wall

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

