

# 1240DZ

---

Splice for elliptical waveguide 240

## Product Classification

<b>Brand</b>	HELIAX®
<b>Product Type</b>	Elliptical waveguide connector

## General Specifications

<b>Interface</b>	Splice
<b>Body Style</b>	Splice
<b>Material Type</b>	Brass

## Electrical Specifications

<b>Operating Frequency Band</b>	24.0 – 26.5 GHz
<b>Insertion Loss, typical</b>	0.01 dB

## Mechanical Specifications

<b>Attachment Method</b>	Tab-flare   Tool-flare
<b>Inner Contact Plating</b>	Unplated
<b>Outer Contact Plating</b>	Unplated
<b>Pressurizable</b>	Yes

## Dimensions

<b>Length</b>	54.10 mm   2.13 in
<b>Weight</b>	0.30 kg   0.66 lb
<b>Width</b>	39.88 mm   1.57 in

## Environmental Specifications

<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)



## \* Footnotes

**Insertion Loss, typical**  $0.05\sqrt{\text{freq}}$  (GHz) (not applicable for elliptical waveguide)