

2132DCP-1

Pre-tuned WR75 Pressurizable Cover Flange for elliptical waveguide 132

OBSOLETE

Replaced By

2132SC

Fixed-tuned WR75 Pressurizable Cover Flange for elliptical waveguide 132

Product Classification

Brand	HELIAX®
Product Type	Elliptical waveguide connector

General Specifications

Interface	WR75 Cover
Waveguide Size	WR75 WG17 R120
Body Style	Straight, pre-tuned
Material Type	Brass

Electrical Specifications

Operating Frequency Band	14.0 – 14.5 GHz
Insertion Loss, typical	0.01 dB
Peak Power, maximum at Frequency	36.60 kW @ 14.70 GHz

Mechanical Specifications

Attachment Method	Tab-flare Tool-flare
Inner Contact Plating	Unplated
Outer Contact Plating	Unplated
Pressurizable	Yes

Dimensions

Length	91.19 mm 3.59 in
Transition Length	56.64 mm 2.23 in
Weight	0.70 kg 1.54 lb
Width	52.32 mm 2.06 in

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)

* Footnotes

Insertion Loss, typical $0.05\sqrt{\text{freq}}$ (GHz) (not applicable for elliptical waveguide)