



AIR FOSC Fiber Optic Splice Closure, Gel Cable Sealing, Aerial, Size B, no pre-installed fiber trays, without grounding

- In-line, free breathing gel-sealed closure for splicing drop cables to distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Product Type	In-line, rectangular fiber closure
Regional Availability	Latin America North America
Product Series	AIR FOSC
Product Brand	FOSC™

General Specifications

Splicing Capacity, Mass Fusion, maximum	288
Splicing Capacity, Single Fusion, maximum	96
Color	Black
Network Area Type	Drop
Package, quantity	1
Packaging Type	Box Carton
Splice Tray Included, quantity	0
Splicing Capacity, Single Splice, 12 fibers, maximum	96
Splicing Capacity, Single Splice, 6 fibers, maximum	48

Dimensions

Main Cable Diameter, maximum	32.00 mm
Length	901.70 mm 35.50 in
Weight	2.27 kg 5.00 lb

Mechanical Specifications

Cable Sealing Type	Compressed gel
Cable Entry Drop Port Style	Round
Cable Entry Main Port Style	Round
Cable Ports, quantity	4
Closure Sealing Type	Free breathing with bolts
Closure Style	In-line
Material Type	Rodent-proof plastic
Mount Type	Strand

Environmental Specifications

Environmental Space

Above ground

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

