

FST-S-HH04-N00-4



FST Flexible Service Terminal, 4 Port, 4 Full-size hardened Adapters at drop side, 1x4 Splitter, 1 Full-size Adapter at input side, 1.5 ft long

- Flexible Service Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-terminated and environmentally sealed for use in optical drop cable deployments
- Flexible structure plus very small branching unit, allowing installation in constrained spaces
- Output cables are staggered, optimizing distributed space consumption and minimizing cable kinking

Product Classification

Product Type	Access terminal, with splitter
Product Series	FST-S
Regional Availability	Asia Latin America North America


General Specifications

Distribution Type	1 x 4 splitter
Port, quantity	4
Port Type	Hardened full-size SC/APC
Stub Type	Hardened full-size SC/APC
Cable, quantity	5
Enclosure Color	Black
Includes	Optical splitter (1)
Package, quantity	1
Packaging Type	Box Carton
Splitter, quantity	1

Dimensions

Cable Length	0.46 m 1.50 ft
Weight, without cable	0.23 kg 0.50 lb

Dimension Drawing



Mechanical Specifications

Enclosure Material Type	Engineered plastic
Mount Type	Handhole Pedestal

Optical Specifications

Directivity, minimum	60 dB
Fiber Type	G.657.A2
Insertion Loss, Splitter, maximum	7.1 dB
Insertion Loss, Splitter, typical	6.7 dB
Insertion Loss, Stub Connector, maximum	0.40 dB
Insertion Loss, Stub Connector, typical	0.16 dB
Insertion Loss, Terminal Connector, maximum	0.40 dB
Insertion Loss, Terminal Connector, typical	0.16 dB
Return Loss, Connector, minimum	65 dB
Return Loss, Splitter, minimum	55 dB
Uniformity, maximum	1.00 dB
Wavelength Range	1260–1650 nm

Environmental Specifications

Environmental Space	Above ground Below ground Buried
Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Qualification Standard	IEC 60529, IP68 + 3 m waterhead Telcordia GR-3120-CORE Telcordia GR-3152-CORE Telcordia GR-326-CORE

UV Resistance

UV stabilized

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system

