

FEC-432RM



Fiber Optic Entrance Cabinet, 432 stranded fibers, 1296 ribbon fibers, single standard drawer

- Provides splicing, administration and storage for outside plant (OSP) and intrafacility cables (IFC)
- Offers a cost-effective, space-saving alternative to splicing on the fiber frame
- Cabinets are designed for deployment in a building equipment area
- Bend radius protection and discrete subunit routing paths ensure easy installation
- Can deploy high count of stranded or ribbon fiber cables

Product Classification

Product Series	FEC
Product Type	Fiber entrance cabinet
Regional Availability	Australia/New Zealand Latin America North America

Dimensions

Depth	381.00 mm 15.00 in
Height	914.40 mm 36.00 in
Width	660.40 mm 26.00 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

General Specifications

Color	Putty white
Includes	Grommets
Splice Drawers, quantity	18
Splice Trays Included, quantity	0
Splicing Capacity, maximum	1296

Mechanical Specifications

Access	Front
Cable Entry Location	Bottom Top
Cable Exit Location	Side
Mount Type	Rack, EIA 23 in

Regulatory Compliance/Certifications

Agency	RoHS 2011/65/EU
---------------	-----------------

Classification

