

F1-PNMSM-2M-HF



FSJ1-50A Jumper with interface types SMA Male and N Male, 2 m

Product Classification

Product Series FSJ1-50A
Product Type SureFlex® standard

General Specifications

Body Style, Connector A Straight
Body Style, Connector B Straight
Interface, Connector A SMA Male
Interface, Connector B N Male
Length 2.000 m | 6.562 ft
Nominal Size 1/4 in
Attachment, Connector A Field attachment
Attachment, Connector B Field attachment
Specification Sheet Revision Level A

Environmental Specifications

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Jumper Assembly Sample Label

Batch 0123456789 **Manufacturing Plant** US22 **Manufacturing Date** (two digit year and week) 1240 **Product Revision** /A

COMMScope Andrew Solutions™
F4-DMDM-2M-D **Part Number**
2 M (6.562 FT)
SUREFLEX ASSEMBLY
U.S. PATENT 5802710
Product of UNITED STATES **12US220001242** **Serial Number**

F1-PNMSM-2M-HF

Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
7500–8500 MHz	1.29	18.00

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)



Included Products

FSJ1-50A — FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

F1TSM-C — SMA Male for 1/4 in FSJ1-50A cable

F1TNM-HC — Type N Male for 1/4 in FSJ1-50A cable

F1TQM-HC — QMA Male for 1/4 in FSJ1-50A cable

FSJ1RK-50B — FSJ1-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket, B2ca s1a dO a1 Compliant

35422-75 — Heat Treated FSJ1RK-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket

35422-33 — Heat Treated FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE Jacket