

# F1-PNMMU-8

---

FSJ1-50A Jumper with interface types N Male and MINI UHF MALE, 2.44 m

## Product Classification

<b>Product Series</b>	FSJ1-50A
<b>Product Type</b>	SureFlex® standard

## General Specifications

<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	N Male
<b>Interface, Connector B</b>	Mini UHF Male
<b>Length</b>	2.438 m   8.000 ft
<b>Nominal Size</b>	1/4 in
<b>Attachment, Connector A</b>	Factory attached
<b>Attachment, Connector B</b>	Field attachment
<b>Specification Sheet Revision Level</b>	A


## Electrical Specifications

<b>DTF, Connector A</b>	-28.00 dB
<b>DTF, Connector B</b>	-10.00 dB

## Environmental Specifications

<b>Immersion Test Method</b>	Meets IEC 60529:2001, IP68 in mated condition
------------------------------	---

## Jumper Assembly Sample Label



## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

FSJ1-50A — FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket

F1MU — Mini UHF Male for 1/4 in FSJ1-50A cable

FSJ1RK-50B — FSJ1-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket, B2ca s1a dO a1 Compliant

35422-75 — Heat Treated FSJ1RK-50B, HELIAX® Superflexible Foam Coaxial Cable, corrugated copper, 1/4 in, black non-halogenated, fire retardant polyolefin jacket

35422-33 — Heat Treated FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE Jacket