



## FTUO Fiber Termination Unit Outdoor Wall Box with universal splice holder for 8 splices

- Typically used as a transition point where the OSP cable is spliced to an indoor cable
- Allows the installation of fibers with a minimum bend radius of 25 mm over a length of 2m
- In-line and single-ended enclosure configuration possible for main cable
- Cable inlet is provided at the bottom left side. Optionally the main cable can continue at the top left side
- Universal splice holder can hold SMOUV and ANT splice protector types

### Product Classification

<b>Product Type</b>	Fiber wall box
<b>Product Series</b>	FTUO
<b>Regional Availability</b>	EMEA

### General Specifications

<b>Application</b>	For drop cables up to 5 mm diameter   For main cables up to 12 mm diameter
<b>Enclosure Color</b>	Gray
<b>Functionality</b>	Splicing
<b>Includes</b>	Hook and loop fastener   Rubber seal   Silicone tube   Splice protector holder   Tie wraps
<b>Minimum Order Quantity</b>	10
<b>Package, quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Splicing Capacity, maximum</b>	8

### Dimensions

<b>Depth</b>	33.00 mm   1.30 in
<b>Height</b>	168.00 mm   6.61 in
<b>Width</b>	132.00 mm   5.20 in

### Mechanical Specifications

<b>Access</b>	Front
<b>Cable Entry Location</b>	Back   Bottom left   Bottom right   Top left   Top right
<b>Cable Ports, quantity</b>	5
<b>Enclosure Material Type</b>	Polycarbonate + ASA
<b>Lock Type</b>	Locking screw
<b>Mount Type</b>	Wall

### Environmental Specifications

<b>Environmental Space</b>	Outdoor
<b>Flammability Rating</b>	UL 94 V-0
<b>Qualification Standard</b>	IEC 60529, IP40 when cable enters from top   IEC 60529, IP43 when cable enters from bottom
<b>UV Resistance</b>	UV stabilized

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

