

APT-NFNF-DB



Arrestor Plus® Dual Band Quarterwave Surge Arrestor (T-shaped, Cylindrical), 800–2170 MHz, with interface types N Female and N Female

Product Classification

Brand	Arrestor Plus®
Product Type	Surge arrestor

General Specifications


Interface	N Female
Interface 2	N Female
Device Type	dc Block
Ordering Note	CommScope® non-standard product

Electrical Specifications

Operating Frequency Band	1710 – 2000 MHz 2000 – 2170 MHz 806 – 824 MHz 824 – 960 MHz
3rd Order IMD	-117.0 dBm -160.0 dBc
3rd Order IMD Test Method	Two +43 dBm carriers
Average Power	600.0 W @ 900 MHz
Connector Impedance	50 ohm
Lightning Surge Capability	100 times @ 20 kA
Lightning Surge Capability Test Method	IEEE C62.42-1991
Lightning Surge Capability Waveform	8/20 waveform
Lightning Surge Current	30 kA
Lightning Surge Current Waveform	8/20 waveform
Peak Power, maximum	10.00 kW
Throughput Energy at Current	2.0 mJ @ 30 kA 25.0 µJ @ 2 kA
Throughput Energy Waveform	8/20 waveform
Insertion Loss, typical	0.07 dB

APT-NFNF-DB

Outline Drawing



Mechanical Specifications

Attachment Durability	25 cycles
Inner Contact Plating	Gold
Interface Durability	500 cycles
Interface Durability Method	IEC 61169-16:9.5
Outer Contact Plating	Trimetal
Pressurizable	No

Dimensions

Height	74.23 mm 2.92 in
Length	73.42 mm 2.89 in
Weight	0.40 kg 0.88 lb
Width	24.89 mm 0.98 in

APT-NFNF-DB

Environmental Specifications

Corrosion Test Method	MIL-STD-202, Method 101, Test Condition B
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Mechanical Shock Test Method	MIL-STD-202F, Method 213B, Test Condition C
Moisture Resistance Test Method	MIL-STD-202, Method 106
Operating Temperature	-40 °C to +150 °C (-40 °F to +302 °F)
Storage Temperature	-40 °C to +100 °C (-40 °F to +212 °F)
Thermal Shock Test Method	MIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 °C
Vibration Test Method	GR 2846-CORE
Water Jetting Test Mating	Mated

Standard Conditions

Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F

Return Loss/VSWR

Frequency Band	VSWR	Return Loss (dB)
806–824 MHz	1.15	23.00
824–960 MHz	1.13	24.00
1710–2000 MHz	1.1	26.40
2000–2170 MHz	1.13	24.00

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)



* Footnotes

Immersion Depth	Immersion at specified depth for 24 hours
Insertion Loss, typical	0.05v*freq (GHz) (not applicable for elliptical waveguide)