

# APT-NFNM-DB



Arrestor Plus® Dual Band Quarterwave Surge Arrestor (T-shaped, Cylindrical), 806–2170 MHz, with interface types N Female and N Male

## Product Classification

<b>Brand</b>	Arrestor Plus®
<b>Product Type</b>	Surge arrester

## General Specifications


<b>Interface</b>	N Female
<b>Interface 2</b>	N Male
<b>Device Type</b>	dc Block
<b>Ordering Note</b>	CommScope® standard product in Asia Pacific

## Electrical Specifications

<b>Operating Frequency Band</b>	1710 – 2000 MHz   2000 – 2170 MHz   806 – 960 MHz   960 – 1710 MHz
<b>3rd Order IMD</b>	-117.0 dBm   -160.0 dBc
<b>3rd Order IMD Test Method</b>	Two +43 dBm carriers
<b>Average Power</b>	600.0 W @ 900 MHz
<b>Connector Impedance</b>	50 ohm
<b>Lightning Surge Capability</b>	100 times @ 20 kA
<b>Lightning Surge Capability Test Method</b>	IEEE C62.42-1991
<b>Lightning Surge Capability Waveform</b>	8/20 waveform
<b>Lightning Surge Current</b>	30 kA
<b>Lightning Surge Current Waveform</b>	8/20 waveform
<b>Peak Power, maximum</b>	10.00 kW
<b>Throughput Energy at Current</b>	2.0 mJ @ 30 kA 25.0 µJ @ 2 kA
<b>Throughput Energy Waveform</b>	8/20 waveform
<b>Insertion Loss, typical</b>	0.07 dB

# APT-NFNM-DB

## Outline Drawing



## Mechanical Specifications

<b>Attachment Durability</b>	25 cycles
<b>Coupling Nut Proof Torque</b>	4.52 N-m   40.00 in lb
<b>Coupling Nut Retention Force</b>	444.82 N   100.00 lbf
<b>Coupling Nut Retention Force Method</b>	MIL-C-39012C-3.25, 4.6.22
<b>Inner Contact Plating</b>	Gold
<b>Interface Durability</b>	500 cycles
<b>Interface Durability Method</b>	IEC 61169-16:9.5
<b>Outer Contact Plating</b>	Trimetal
<b>Pressurizable</b>	No

## Dimensions

<b>Height</b>	74.23 mm   2.92 in
<b>Length</b>	79.84 mm   3.14 in
<b>Weight</b>	0.43 kg   0.95 lb
<b>Width</b>	24.89 mm   0.98 in

## Environmental Specifications

# APT-NFNM-DB

---

<b>Corrosion Test Method</b>	MIL-STD-202, Method 101, Test Condition B
<b>Immersion Depth</b>	1 m
<b>Immersion Test Mating</b>	Mated
<b>Immersion Test Method</b>	IEC 60529:2001, IP68
<b>Mechanical Shock Test Method</b>	MIL-STD-202F, Method 213B, Test Condition C
<b>Moisture Resistance Test Method</b>	MIL-STD-202, Method 106
<b>Operating Temperature</b>	-40 °C to +150 °C (-40 °F to +302 °F)
<b>Storage Temperature</b>	-40 °C to +100 °C (-40 °F to +212 °F)
<b>Thermal Shock Test Method</b>	MIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 °C
<b>Vibration Test Method</b>	GR 2846-CORE
<b>Water Jetting Test Mating</b>	Mated

## Standard Conditions

<b>Attenuation, Ambient Temperature</b>	20 °C   68 °F
<b>Average Power, Ambient Temperature</b>	40 °C   104 °F

## Return Loss/VSWR

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
806–960 MHz	1.1	26.40
960–1710 MHz	1.15	23.00
1710–2000 MHz	1.1	26.40
2000–2170 MHz	1.15	23.00

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)



## \* Footnotes

<b>Immersion Depth</b>	Immersion at specified depth for 24 hours
<b>Insertion Loss, typical</b>	$0.05\sqrt{\text{freq}} \text{ (GHz)}$ (not applicable for elliptical waveguide)