

# APTDC-BDFDF-DB



Arrestor Plus® LTE Band Quarterwave dc Passing Surge Arrestor (T-shaped), 698–2170 MHz, with interface types DIN Female Bulkhead and DIN Female

## Product Classification

<b>Brand</b>	Arrestor Plus®
<b>Product Type</b>	Surge arrestor


## General Specifications

<b>Interface</b>	7-16 DIN Female Bulkhead
<b>Interface 2</b>	7-16 DIN Female
<b>Device Type</b>	dc Pass
<b>Ordering Note</b>	CommScope® standard product in the United States and Canada
<b>Body Style</b>	Bulkhead

## Electrical Specifications

<b>Operating Frequency Band</b>	698 – 2170 MHz
<b>3rd Order IMD</b>	-117.0 dBm   -160.0 dBc
<b>3rd Order IMD Test Method</b>	Two +43 dBm carriers
<b>Average Power</b>	3000 W
<b>Connector Impedance</b>	50 ohm
<b>Gas Tube Voltage</b>	350 V
<b>Lightning Surge Capability</b>	10 times @ 30 kA
<b>Lightning Surge Capability Test Method</b>	IEEE C62.42-1991
<b>Lightning Surge Capability Waveform</b>	8/20 waveform
<b>Lightning Surge Current</b>	30 kA
<b>Lightning Surge Current Waveform</b>	8/20 waveform
<b>Peak Power, maximum</b>	40.00 kW
<b>Insertion Loss, typical</b>	0.05 dB

## Outline Drawing



## Mechanical Specifications

<b>Attachment Durability</b>	25 cycles
<b>Inner Contact Plating</b>	Silver
<b>Interface Durability</b>	500 cycles
<b>Interface Durability Method</b>	IEC 61169-16:9.5
<b>Outer Contact Plating</b>	Trimetal
<b>Pressurizable</b>	No

## Dimensions

<b>Height</b>	81.03 mm   3.19 in
<b>Length</b>	87.88 mm   3.46 in
<b>Weight</b>	0.64 kg   1.41 lb
<b>Width</b>	41.91 mm   1.65 in

## Environmental Specifications

<b>Corrosion Test Method</b>	MIL-STD-202, Method 101, Test Condition B
<b>Immersion Depth</b>	1 m
<b>Immersion Test Mating</b>	Mated
<b>Immersion Test Method</b>	IEC 60529:2001, IP68
<b>Mechanical Shock Test Method</b>	MIL-STD-202F, Method 213B, Test Condition C
<b>Moisture Resistance Test Method</b>	MIL-STD-202, Method 106

# APTDC-BDFDF-DB

---

<b>Operating Temperature</b>	-40 °C to +100 °C (-40 °F to +212 °F)
<b>Storage Temperature</b>	-70 °C to +150 °C (-94 °F to +302 °F)
<b>Thermal Shock Test Method</b>	MIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 °C
<b>Water Jetting Test Mating</b>	Mated

## Standard Conditions

<b>Attenuation, Ambient Temperature</b>	20 °C   68 °F
<b>Average Power, Ambient Temperature</b>	40 °C   104 °F

## Return Loss/VSWR

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
1.0–5.0 MHz	1.17	-22.00
2.0–2.3 MHz	1.12	-25.00
698–806 MHz	1.13	-20.50
806–960 MHz	1.13	-24.00
1710–2000 MHz	1.11	-26.00
2000–2170 MHz	1.11	-26.00

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
AISG	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

<b>Immersion Depth</b>	Immersion at specified depth for 24 hours
<b>Insertion Loss, typical</b>	0.05vfreq (GHz) (not applicable for elliptical waveguide)