


GigaSPEED X10D® 1291B ETL Verified Category 6A F/UTP Cable, non-plenum, slate jacket, 4 pair count, 1000 ft (305 m) length, reel

Product Classification

Portfolio	SYSTIMAX®
Brand	GigaSPEED X10D®
Product Type	Twisted pair cable
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Cross Section Drawing



Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Drain Wire Material	Tinned copper
Insulation Material	Polyolefin
Separator Material	Polyolefin
Shield (Tape) Material	Polyester/Aluminum shield

Dimensions

Cable Length	305 m 1000 ft
---------------------	-----------------

Cable Weight	35.00 lb/kft
Diameter Over Jacket, nominal	7.518 mm 0.296 in
Jacket Thickness	0.508 mm 0.020 in

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance Unbalance, maximum	4 %
dc Resistance, maximum	8.00 ohms/100 m
Mutual Capacitance	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	68 %
Operating Frequency, maximum	500 MHz
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2
Dielectric Strength, minimum	1500 Vac 2500 Vdc

Environmental Specifications

Environmental Space	Non-plenum
Flame Test Method	CMR
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	F/UTP (shielded)
Packaging Type	Reel
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	Slate
Product Number	1291B
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Drain Wire Gauge	24 AWG
Drain Wire Type	Solid
Separator Type	Isolator

Mechanical Specifications

Pulling Tension, maximum	11 kg 25 lb
---------------------------------	---------------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

