

TeraSPEED® 2.9 mm Plenum Zipcord Cable


Product Classification

Portfolio	CommScope®
Product Type	Fiber indoor cable
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Standards And Qualifications

Cable Qualification Standards	ANSI/ICEA S-83-596 Telcordia GR-409
--------------------------------------	---------------------------------------

Representative Image



General Specifications

Cable Type	Cordage
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	G.652.D and G.657.A1 , TeraSPEED®
Total Fiber Count	2

Fiber Type	G.652.D and G.657.A1, TeraSPEED®
Fiber Type, quantity	2
Jacket Color	Yellow

Dimensions

Cable Weight	13.4 lb/kft 20.0 kg/km
Height Over Jacket	2.90 mm 0.11 in
Width Over Jacket	5.90 mm 0.23 in

Physical Specifications

Minimum Bend Radius, loaded	4.4 cm 1.7 in
Minimum Bend Radius, unloaded	2.3 cm 0.9 in
Tensile Load, long term, maximum	27 lbf 120 N
Tensile Load, short term, maximum	90 lbf 400 N
Vertical Rise, maximum	500.0 m 1640.4 ft

Flame Test Specifications

Flame Test Listing	NEC OFNP (ETL) and c(ETL)
Flame Test Method	NFPA 262

Environmental Specifications

Environmental Space	Plenum
Installation Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression	10 N/mm 57 lb/in
Compression Test Method	FOTP-41 IEC 60794-1 E3
Flex	300 cycles
Flex Test Method	FOTP-104 IEC 60794-1 E6
Impact	0.55 ft lb 0.74 N-m
Impact Test Method	FOTP-25 IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1 E7

Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable