

# CNT-240-R



CNT-240, CNT® 50 Ohm Braided Coaxial Cable, black fire retardant riser rated PVC jacket

## Product Classification

<b>Brand</b>	CNT®
<b>Product Series</b>	CNT-240
<b>Product Type</b>	Braided coaxial cable

## Construction Materials

<b>Jacket Color</b>	Black
<b>Jacket Material</b>	Fire retardant PVC
<b>Braid Material</b>	Tinned copper
<b>Shield Tape Material</b>	Aluminum
<b>Dielectric Material</b>	Foam PE
<b>Inner Conductor Material</b>	Copper

## Dimensions

<b>Cable Weight</b>	0.05 kg/m
<b>Diameter Over Dielectric</b>	3.810 mm   0.150 in
<b>Diameter Over Jacket</b>	6.100 mm   0.240 in
<b>Diameter Over Tape</b>	3.988 mm   0.157 in
<b>Inner Conductor OD</b>	1.4200 mm   0.0559 in
<b>Nominal Size</b>	0.240 in
<b>Outer Conductor OD</b>	4.520 mm   0.178 in

## Electrical Specifications

<b>Cable Impedance</b>	50 ohm
<b>Capacitance</b>	79.4 pF/m   24.2 pF/ft
<b>dc Resistance, Inner Conductor</b>	11.100 ohms/km   3.384 ohms/kft
<b>dc Resistance, Outer Conductor</b>	12.760 ohms/km   3.890 ohms/kft
<b>dc Test Voltage</b>	2500 V
<b>Jacket Spark Test Voltage (rms)</b>	2500 V
<b>Maximum Frequency</b>	31.00 GHz
<b>Operating Frequency Band</b>	30 – 6000 MHz
<b>Peak Power</b>	5.6 kW
<b>Velocity</b>	84%

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
------------------------------	--------------------------------------

# CNT-240-R

---

## General Specifications

<b>Cable Type</b>	CNT-240
<b>Braid Coverage</b>	90% braid
<b>Packaging Type</b>	Reel

## Mechanical Specifications

<b>Fire Retardancy Test Method</b>	UL 1666/CATVR
<b>Minimum Bend Radius, Single Bend</b>	19.10 mm   0.75 in
<b>Tensile Strength</b>	36 kg   80 lb

## Electrical Performance

Frequency	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
30 MHz	4.90	1.50
50 MHz	6.20	1.90
150 MHz	10.20	3.10
220 MHz	12.50	3.80
450 MHz	17.40	5.30
900 MHz	24.90	7.60
1800 MHz	35.75	10.90
2500 MHz	42.31	12.90
3000 MHz	46.48	14.17
4000 MHz	53.92	16.44
4500 MHz	57.30	17.47
5000 MHz	60.51	18.45
5200 MHz	61.76	18.83
5500 MHz	63.60	19.39
5800 MHz	66.90	20.40
6000 MHz	73.82	22.50

\* Values typical, guaranteed within 5%

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2015  
China RoHS SJ/T 11364-2014

### Classification

Compliant  
Designed, manufactured and/or distributed under this quality management system  
Below Maximum Concentration Value (MCV)

