

# AVA7P-50-43B



AVA7-50, HELIAX® Andrew Virtual Air™ Premium Coaxial Cable, corrugated copper, 1-5/8 in, black PE jacket

## Product Classification

<b>Brand</b>	HELIAX®
<b>Product Series</b>	AVA7-50
<b>Product Type</b>	Coaxial wireless cable

## Standards And Qualifications

<b>EN50575 CPR Cable EuroClass</b>	Fca
------------------------------------	-----

## Construction Materials

<b>Jacket Material</b>	PE
<b>Outer Conductor Material</b>	Corrugated copper
<b>Dielectric Material</b>	Foam PE
<b>Flexibility</b>	Standard
<b>Inner Conductor Material</b>	Corrugated copper tube
<b>Jacket Color</b>	Black

## Dimensions

<b>Nominal Size</b>	1-5/8 in
<b>Cable Weight</b>	0.72 lb/ft   1.07 kg/m
<b>Diameter Over Dielectric</b>	44.450 mm   1.750 in
<b>Diameter Over Jacket</b>	51.054 mm   2.010 in
<b>Inner Conductor OD</b>	18.1610 mm   0.7150 in
<b>Outer Conductor OD</b>	46.355 mm   1.825 in

## Electrical Specifications

<b>Cable Impedance</b>	50 ohm $\pm$ 1 ohm
<b>Capacitance</b>	22.0 pF/ft   72.2 pF/m
<b>dc Resistance, Inner Conductor</b>	0.410 ohms/kft   1.435 ohms/km
<b>dc Resistance, Outer Conductor</b>	0.160 ohms/kft   0.525 ohms/km
<b>dc Test Voltage</b>	15000 V

# AVA7P-50-43B

---

<b>Inductance</b>	0.187 $\mu\text{H}/\text{m}$   0.057 $\mu\text{H}/\text{ft}$
<b>Insulation Resistance</b>	100000 Mohms•km
<b>Jacket Spark Test Voltage (rms)</b>	10000 V
<b>Operating Frequency Band</b>	1 – 2700 MHz
<b>Peak Power</b>	302.0 kW
<b>Velocity</b>	92%

## Environmental Specifications

<b>Installation Temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +85 °C (-94 °F to +185 °F)

## General Specifications

<b>Ordering Note</b>	Not available in the United States or Canada
----------------------	--

## Mechanical Specifications

<b>Bending Moment</b>	47.5 N-m   35.0 ft lb
<b>Flat Plate Crush Strength</b>	90.0 lb/in   1.6 kg/mm
<b>Minimum Bend Radius, Multiple Bends</b>	381.00 mm   15.00 in
<b>Minimum Bend Radius, Single Bend</b>	203.20 mm   8.00 in
<b>Number of Bends, minimum</b>	15
<b>Number of Bends, typical</b>	50
<b>Tensile Strength</b>	181 kg   400 lb

## Note

<b>Performance Note</b>	Values typical, unless otherwise stated
-------------------------	---

## Standard Conditions

<b>Attenuation, Ambient Temperature</b>	20 °C   68 °F
<b>Average Power, Ambient Temperature</b>	40 °C   104 °F
<b>Average Power, Inner Conductor Temperature</b>	100 °C   212 °F

## Return Loss/VSWR

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
710–806 MHz	1.20	20.80
806–970 MHz	1.15	23.13
1420–1530 MHz	1.15	23.13
1700–2180 MHz	1.15	23.13
2535–2655 MHz	1.20	20.80

## Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
0.5	0.044	0.013	166.49
1	0.062	0.019	117.56
1.5	0.076	0.023	95.88
2	0.088	0.027	82.96
10	0.197	0.06	36.78
20	0.281	0.086	25.84
30	0.346	0.105	21.00
50	0.45	0.137	16.14
85	0.593	0.181	12.25
88	0.603	0.184	12.03
100	0.645	0.197	11.26
108	0.672	0.205	10.81
150	0.798	0.243	9.09
174	0.864	0.263	8.41
200	0.93	0.284	7.81
204	0.94	0.287	7.72
300	1.156	0.352	6.28
400	1.351	0.412	5.37
450	1.441	0.439	5.04
460	1.459	0.445	4.98
460	1.459	0.445	4.98
500	1.527	0.465	4.76
512	1.547	0.471	4.69
600	1.689	0.515	4.30
700	1.84	0.561	3.95
800	1.982	0.604	3.66
824	2.016	0.614	3.60
894	2.11	0.643	3.44
960	2.197	0.67	3.30
1000	2.249	0.685	3.23
1218	2.517	0.767	2.89
1250	2.554	0.779	2.84
1500	2.838	0.865	2.56
1700	3.053	0.93	2.38
1794	3.151	0.96	2.30
1800	3.157	0.962	2.30
2000	3.359	1.024	2.16
2100	3.457	1.054	2.10
2200	3.554	1.083	2.04
2300	3.649	1.112	1.99
2500	3.836	1.169	1.89
2700	4.017	1.224	1.81

\* Values typical, guaranteed within 5%

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

CENELEC

**Classification**

Compliant

EN 50575 compliant, Declaration of Performance (DoP) available

