

PowerSUM 3061A ETL Verified Category 5e U/UTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1000 ft (305 m) length, WE TOTE® box


Product Classification

Portfolio	SYSTIMAX®
Brand	PowerSUM
Product Type	Twisted pair cable
Regional Availability	Asia Australia/New Zealand EMEA Latin America

Standards And Qualifications

EN50575 CPR Cable EuroClass	Dca s2 d2 a1
------------------------------------	--------------------

Cross Section Drawing



Construction Materials

Jacket Material	Low Smoke Zero Halogen (LSZH)
Conductor Material	Bare copper
Insulation Material	Polyolefin

Dimensions

Cable Length	305 m 1000 ft
Cable Weight	20.00 lb/kft
Diameter Over Jacket, nominal	5.207 mm 0.205 in
Jacket Thickness	0.533 mm 0.021 in

Electrical Specifications

ANSI/TIA Category	5e
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m
Mutual Capacitance	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	69 %
Operating Frequency, maximum	200 MHz
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-3-1 ISO/IEC 11801 Class D

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Smoke Test Method	IEC 61034-2
Acid Gas Test Method	IEC 60754-2
Flame Test Method	IEC 60332-3-22
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	U/UTP (unshielded)
Packaging Type	WE TOTE® box
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	White
Product Number	3061A
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

Mechanical Specifications

Pulling Tension, maximum	11 kg 25 lb
---------------------------------	---------------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015
CENELEC

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system
EN 50575 compliant, Declaration of Performance (DoP) available

