

RCT6-LT-1A-RNA



RCT6, RADIAX® Coaxial Radiating Cable with Bump, 50–900 MHz, tuned foil, 1-1/4 in, black non-halogenated, fire retardant polyolefin jacket

Product Classification

Brand	RADIAX®
Product Series	RCT6
Product Type	Radiating cable

Construction Materials

Jacket Material	Non-halogenated, fire retardant polyolefin
Dielectric Material	Foam PE
Inner Conductor Material	Corrugated copper tube
Jacket Color	Black
Outer Conductor Material	Copper foil

Dimensions

Nominal Size	1-1/4 in
Inner Conductor OD	0.5200 in 14.2080 mm
Outer Conductor OD	1.340 in 34.030 mm
Diameter Over Jacket	39.116 mm 1.540 in
Cable Weight	0.43 lb/ft 0.64 kg/m

Electrical Specifications

Operating Frequency Band	50 – 900 MHz
Optimum Operating Frequency Band	70 – 500 MHz
Polarization	Horizontal
VSWR Installed, typical, 50–960 MHz	1.30
VSWR on Reel, typical	1.43
Stop Bands	295 – 335 MHz 610 – 664 MHz
Cable Impedance	50 ohm ±2 ohm
dc Resistance, Inner Conductor	0.530 ohms/kft 1.740 ohms/km
dc Resistance, Outer Conductor	0.900 ohms/kft 2.953 ohms/km
dc Test Voltage	8500 V
Insulation Resistance	100000 Mohms•km
Jacket Spark Test Voltage (rms)	10000 V

RCT6-LT-1A-RNA

Peak Power	180.0 kW
Velocity	91%

Environmental Specifications

Installation Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-30 °C to +80 °C (-22 °F to +176 °F)
Storage Temperature	-30 °C to +80 °C (-22 °F to +176 °F)

General Specifications

Cable Type	Radiating Mode (RCT) Series
-------------------	-----------------------------

Mechanical Specifications

Bending Moment	15.5 N-m 11.4 ft lb
Flat Plate Crush Strength	80.0 lb/in 1.4 kg/mm
Indication of Slot Alignment	Yes; bumps face the wall
Minimum Bend Radius, Single Bend	381.00 mm 15.00 in
Recommended Distance from the Wall	101.6 mm 4.0 in
Recommended Hanger Spacing	1.3 m 4.3 ft
Tensile Strength	168 kg 370 lb
Fire Retardancy Test Method	IEC 60332-1 IEC 60332-3C-24
Smoke Index Test Method	IEC 61034
Toxicity Index Test Method	IEC 60754-1 IEC 60754-2

Standard Conditions

Attenuation Test Method	IEC 61196-4
Attenuation Tolerance	±5%
Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F
Average Power, Inner Conductor Temperature	100 °C 212 °F
Coupling Loss Test Method	IEC 61196-4
Coupling Loss Tolerance	±5 dB

Electrical Performance

Frequency	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Coupling Loss 50%	Coupling Loss 95%
75 MHz	0.70	0.21	63	74
100 MHz	0.80	0.24	55	67
150 MHz	1.00	0.30	67	77
350 MHz	1.80	0.55	56	59
400 MHz	1.90	0.58	56	59
450 MHz	2.00	0.61	62	68
500 MHz	2.10	0.64	53	55

RCT6-LT-1A-RNA

800 MHz	3.50	1.10	54	62
900 MHz	4.20	1.28	52	65

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

