

Fiber Optic Cable, 16-fiber, OM3, 1000 m, aqua

## **OBSOLETE**

**This product was discontinued on: June 13, 2018**

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA

## Standards And Qualifications

<b>EN50575 CPR Cable EuroClass</b>	Dca   s2   d1   a1
------------------------------------	--------------------

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum</b>	1.00 dB/km @ 1,300 nm   3.50 dB/km @ 850 nm
<b>Standards Compliance</b>	IEC 60794-1   TIA-492AAAC (OM3)

## General Specifications

<b>Cable Type</b>	Tight buffer
-------------------	--------------

## Construction Materials

<b>Total Fiber Count</b>	16
<b>Fiber Type</b>	OM3
<b>Jacket Color</b>	Aqua

## Dimensions

<b>Cable Length</b>	1000 m   3281 ft
<b>Cable Weight</b>	46.0 kg/km   31.0 lb/kft
<b>Diameter Over Jacket</b>	7.50 mm   0.30 in

## Physical Specifications

<b>Minimum Bend Radius, loaded</b>	99.1 mm   3.9 in
<b>Minimum Bend Radius, unloaded</b>	100.1 mm   3.9 in
<b>Tensile Load, long term, maximum</b>	600 N   135 lbf
<b>Tensile Load, short term, maximum</b>	996 N   224 lbf

## Environmental Specifications

<b>Environmental Space</b>	Universal Low Smoke Zero Halogen (ULSZH)
<b>Installation Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available



### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable