

Fiber Optic Cable, 48-fiber, OM3, loose tube, dry, 1000 m, aqua

Product Classification

Portfolio	NETCONNECT®
Product Type	Fiber indoor/outdoor cable
Regional Availability	Asia Australia/New Zealand EMEA

Standards And Qualifications

EN50575 CPR Cable EuroClass	Eca
------------------------------------	-----

Optical Specifications, Wavelength Specific

Attenuation, maximum	1.00 dB/km @ 1300 nm 3.50 dB/km @ 850 nm
Standards Compliance	TIA-492AAAC (OM3)

General Specifications

Cable Type	Loose tube
Subunit Type	Gel-free

Construction Materials

Total Fiber Count	48
Fiber Type	OM3
Fibers per Subunit, quantity	12
Jacket Color	Aqua

Dimensions

Cable Length	1000 m 3281 ft
Cable Weight	105.0 kg/km
Diameter Over Jacket	11.50 mm 0.45 in

Physical Specifications

Minimum Bend Radius, loaded	228.6 mm 9.0 in
Minimum Bend Radius, unloaded	169.9 mm 6.7 in
Tensile Load, long term, maximum	600 N 135 lbf
Tensile Load, short term, maximum	996 N 224 lbf

Environmental Specifications

Environmental Space Universal Low Smoke Zero Halogen (ULSZH)
Operating Temperature -10 °C to +70 °C (+14 °F to +158 °F)

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU CENELEC	Compliant EN 50575 compliant, Declaration of Performance (DoP) available



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable