

Indoor/outdoor Fiber Optic Cable, 4-fiber, OM4, aqua

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA

## Standards And Qualifications

<b>EN50575 CPR Cable EuroClass</b>	Cca   s1   d0   a2
------------------------------------	--------------------

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum (temporary)</b>	0.70 dB/km @ 1,300 nm
<b>Standards Compliance</b>	IEC 60794-1   TIA-492AAAD (OM4)

## General Specifications

<b>Cable Type</b>	Tight buffer
-------------------	--------------

## Construction Materials

<b>Total Fiber Count</b>	4
<b>Fiber Type</b>	OM4
<b>Fibers per Subunit, quantity</b>	4
<b>Jacket Color</b>	Aqua

## Dimensions

<b>Cable Length</b>	2000 m   6562 ft
<b>Cable Weight</b>	27.0 kg/km
<b>Diameter Over Jacket</b>	5.00 mm   0.20 in

## Physical Specifications

<b>Minimum Bend Radius, loaded</b>	75.0 mm   3.0 in
<b>Minimum Bend Radius, unloaded</b>	50.0 mm   2.0 in
<b>Tensile Load, long term, maximum</b>	300 N   67 lbf
<b>Tensile Load, short term, maximum</b>	650 N   146 lbf

## Environmental Specifications

<b>Environmental Space</b>	Universal Low Smoke Zero Halogen (ULSZH)
<b>Installation Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)

**Operating Temperature** -20 °C to +70 °C (-4 °F to +158 °F)  
**Storage Temperature** -20 °C to +70 °C (-4 °F to +158 °F)

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available



### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable