

Indoor Fiber Optic Cable, 6-fiber, OS2, singlemode, tight buffer, yellow

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA

## Standards And Qualifications

<b>EN50575 CPR Cable EuroClass</b>	Dca   s2   d1   a1
------------------------------------	--------------------

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum (temporary)</b>	0.40 dB/km @ 1,550 nm   0.50 dB/km @ 1,310 nm
<b>Standards Compliance</b>	IEC 60794-1   TIA-492CAAB (OS2)

## General Specifications

<b>Cable Type</b>	Tight buffer
-------------------	--------------

## Construction Materials

<b>Total Fiber Count</b>	6
<b>Fiber Type</b>	OS2
<b>Fibers per Subunit, quantity</b>	6
<b>Jacket Color</b>	Yellow

## Dimensions

<b>Cable Length</b>	2000 m   6562 ft
<b>Cable Weight</b>	33.0 kg/km
<b>Diameter Over Jacket</b>	6.00 mm   0.24 in

## Physical Specifications

<b>Minimum Bend Radius, loaded</b>	90.0 mm   3.5 in
<b>Minimum Bend Radius, unloaded</b>	60.0 mm   2.4 in
<b>Tensile Load, long term, maximum</b>	600 N   135 lbf
<b>Tensile Load, short term, maximum</b>	996 N   224 lbf

## Flame Test Specifications

<b>Flame Test Method</b>	IEC 60332-3   IEC 60332-1   IEC 60754-1   IEC 61034-2
--------------------------	---

## Environmental Specifications

<b>Environmental Space</b>	Universal Low Smoke Zero Halogen (ULSZH)
<b>Installation Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Operating Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Storage Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available



### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable