



## FiberGuide® 4-Inch Express Exit™ for 4 x 4, 4 x 6 and 4 x 12 Raceway, yellow

- FiberGuide products are designed and manufactured to ensure total off-frame fiber cable protection
- FiberGuide maintains a minimum bend radius throughout the entire system, regardless the system size
- FiberGuide is an optical raceway system for central office, mobile switching center and data center applications
- Engineers and installers can benefit from the large suite of available FiberGuide design tools

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Portfolio</b>             | CommScope®  |
| <b>Brand</b>                 | FiberGuide®   |
| <b>Product Type</b>          | Fiber raceway drop kit  |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |

## Dimensions

|                          |  |
|--------------------------|--|
| <b>System Dimensions</b> | 100 mm x 100 mm   12 in x 4 in   150 mm x 100 mm   300 mm x 100 mm   4 in x 4 in   6 in x 4 in |
| <b>Height</b>            | 196.00 mm   7.72 in  |
| <b>Width</b>             | 406.00 mm   15.98 in   |

## Environmental Specifications

|                                |                                |
|--------------------------------|--------------------------------|
| <b>Flammability Rating</b>     | CSA S143   UL 2024   UL 94 V-0 |
| <b>Halogen Characteristics</b> | Blue Angel   TCO '99   WEEE    |
| <b>Safety Standard</b>         | CSA   UL                       |

## General Specifications

|              |        |
|--------------|--------|
| <b>Color</b> | Yellow |
|--------------|--------|

## Mechanical Specifications

|                      |                           |
|----------------------|---------------------------|
| <b>Material Type</b> | Engineering Thermoplastic |
|----------------------|---------------------------|

## Regulatory Compliance/Certifications

|               |                 |
|---------------|-----------------|
| <b>Agency</b> | RoHS 2011/65/EU |
|---------------|-----------------|

|                       |           |
|-----------------------|-----------|
| <b>Classification</b> | Compliant |
|-----------------------|-----------|

