




ETL Verified Category 5e U/UTP Cable, plenum, white jacket, 4 pair count, 3000 ft (914 m) length, reel

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Twisted pair cable
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Cross Section Drawing



## Construction Materials

<b>Jacket Material</b>	PVC
<b>Conductor Material</b>	Bare copper
<b>Insulation Material</b>	FEP   Polyolefin

## Dimensions

<b>Cable Length</b>	914 m   3000 ft
<b>Cable Length Tolerance</b>	±5%
<b>Cable Weight</b>	20.41 lb/kft
<b>Diameter Over Jacket, nominal</b>	4.877 mm   0.192 in
<b>Jacket Thickness</b>	0.508 mm   0.020 in

## Electrical Specifications

<b>ANSI/TIA Category</b>	5e
--------------------------	----

<b>Characteristic Impedance</b>	100 ohm
<b>dc Resistance Unbalance, maximum</b>	5 %
<b>dc Resistance, maximum</b>	9.38 ohms/100 m
<b>Delay Skew, maximum</b>	15 ns
<b>Mutual Capacitance at Frequency</b>	5.6 nF/100 m @ 1 kHz
<b>Nominal Velocity of Propagation (NVP)</b>	76 %
<b>Operating Frequency, maximum</b>	200 MHz
<b>Operating Voltage, maximum</b>	80 V
<b>Transmission Standards</b>	ANSI/TIA-568-C.2   CENELEC EN 50288-3-1   ISO/IEC 11801 Class D
<b>Safety Voltage Rating</b>	300 V
<b>Dielectric Strength, minimum</b>	1500 Vac   2500 Vdc
<b>Note</b>	All electrical transmission tests include swept frequency measurements

## Environmental Specifications

<b>Environmental Space</b>	Plenum
<b>Smoke Test Method</b>	CMP
<b>Flame Test Method</b>	CMP   NEC Article 800   NFPA 262   UL 444   UL 910
<b>Installation Temperature</b>	0 °C to +60 °C (+32 °F to +140 °F)
<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)

## General Specifications

<b>Cable Type</b>	U/UTP (unshielded)
<b>Packaging Type</b>	Reel
<b>Pairs, quantity</b>	4
<b>Cable Component Type</b>	Horizontal
<b>Jacket Color</b>	White
<b>Product Number</b>	CS24P
<b>Conductor Gauge, singles</b>	24 AWG
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	8

## Mechanical Specifications

<b>Pulling Tension, maximum</b>	11 kg   25 lb
---------------------------------	---------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Electrical Performance

CS CommScope  
 Std Refers to the standard value listed under Transmission Standards in the Electrical Specifications above  
 Typ Typical  
 IL Insertion Loss (dB/100m)  
 NEXT Near End Crosstalk (dB/100m)  
 ACR Attenuation to Crosstalk Ratio (dB/100m)  
 PSNEXT Power Sum Near End Crosstalk (db/100m)  
 PSACR Power Sum Attenuation to Crosstalk Ratio (dB/100m)  
 ACRF Attenuation to Crosstalk Ratio - Far End (dB/100m)  
 PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)  
 RL Return Loss (dB)

Freq. MHz	IL			NEXT			ACR			PSNEXT			PSACR			ACRF			PSACRF			RL		
	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ	CS	Std	Typ
1	2.0	2.0	2.1	65.3	65.3	81.5	63.3	63.3	79.4	62.3	62.3	79.2	60.3	60.3	77.1	63.8	63.8	76.4	60.8	60.8	74.7	20.0	20.0	33.5
4	4.1	4.1	3.9	56.3	56.3	72.9	52.2	52.2	69.0	53.3	53.3	70.5	49.2	49.2	66.6	51.8	51.8	64.8	48.8	48.8	63.1	23.0	23.0	33.5
8	5.8	5.8	5.5	51.8	51.8	68.3	46.0	46.0	62.7	48.8	48.8	65.9	43.0	43.0	60.4	45.7	45.7	58.9	42.7	42.7	57.2	24.5	24.5	36.6
10	6.5	6.5	6.2	50.3	50.3	66.7	43.8	43.8	60.6	47.3	47.3	64.2	40.8	40.8	58.1	43.8	43.8	57.0	40.8	40.8	55.3	25.0	25.0	36.7
16	8.2	8.2	7.8	47.2	47.2	63.6	39.0	39.0	55.8	44.2	44.2	61.2	36.0	36.0	53.4	39.7	39.7	52.9	36.7	36.7	51.1	25.0	25.0	38.5
20	9.3	9.3	8.7	45.8	45.8	62.0	36.5	36.5	53.2	42.8	42.8	59.5	33.5	33.5	50.8	37.8	37.8	51.0	34.8	34.8	49.2	25.0	25.0	38.8
25	10.4	10.4	9.8	44.3	44.3	60.3	33.9	33.9	50.5	41.3	41.3	57.9	30.9	30.9	48.2	35.8	35.8	48.9	32.8	32.8	47.2	24.3	24.3	39.4
31.25	11.7	11.7	11.0	42.9	42.9	58.9	31.2	31.2	47.9	39.9	39.9	56.6	28.2	28.2	45.7	33.9	33.9	47.0	30.9	30.9	45.2	23.6	23.6	39.8
62.5	17.0	17.0	15.6	38.4	38.4	54.2	21.4	21.4	38.6	35.4	35.4	51.9	18.4	18.4	36.2	27.9	27.9	40.8	24.9	24.9	39.0	21.5	21.5	34.7
100	22.0	22.0	20.0	35.3	35.3	50.9	13.3	13.3	30.9	32.3	32.3	48.6	10.3	10.3	28.6	23.8	23.8	36.9	20.8	20.8	35.1	20.1	20.1	30.9
155	28.1		25.1	32.4		47.8	4.4		22.7	29.4		45.3	1.4		20.2	20.0		33.1	17.0		31.3	18.8		28.3
200	32.4		28.8	30.8		45.6	-1.6		16.8	27.8		43.3	-4.6		14.5	17.8		30.7	14.8		28.8	18.0		27.6
250			32.4			43.7			11.3			41.4			9.1			28.7			26.8			26.9
300			35.7			42.0			6.3			39.7			4.0			27.0			25.1			26.5
350			38.9			40.5			1.6			38.3			-0.6			25.2			23.3			25.6