




Category 5e F/UTP Cable, plenum, white jacket, 4 pair count, 3000 ft (914 m) length, reel

Product Classification

Portfolio	CommScope®
Product Type	Twisted pair cable
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Cross Section Drawing



Construction Materials

Jacket Material	PVC
Conductor Material	Bare copper
Drain Wire Material	Tinned copper
Insulation Material	FEP
Shield (Tape) Material	Aluminum/Polyester

Dimensions

Cable Length	914 m 3000 ft
Cable Weight	29.60 lb/kft
Diameter Over Jacket, nominal	5.969 mm 0.235 in
Jacket Thickness	0.457 mm 0.018 in

Electrical Specifications

ANSI/TIA Category	5e
Characteristic Impedance	100 ohm
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m
Delay Skew, maximum	15 ns
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	73 %
Operating Frequency, maximum	100 MHz
Operating Voltage, maximum	80 V
Transmission Standards	ANSI/TIA-568-C.2 CENELEC EN 50288-6-1 ISO/IEC 11801 Class E
Safety Voltage Rating	300 V
Dielectric Strength, minimum	1500 Vac 2500 Vdc
Note	All electrical transmission tests include swept frequency measurements

Environmental Specifications

Environmental Space	Plenum
Flame Test Method	CMP NEC Article 800 NFPA 262 UL 444 UL 910
Installation Temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	F/UTP (shielded)
Packaging Type	Reel
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	White
Product Number	CS24P
Conductor Gauge, singles	24 AWG
Conductor Type, singles	Solid
Conductors, quantity	8
Drain Wire Gauge	24 AWG
Drain Wire Type	Solid

Mechanical Specifications

Pulling Tension, maximum	11 kg 25 lb
---------------------------------	---------------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system



Electrical Performance

Std Refers to the standard value listed under Transmission Standards in the Electrical Specifications above

Typ Typical

IL Insertion Loss (dB/100m)

NEXT Near End Crosstalk (dB/100m)

ACR Attenuation to Crosstalk Ratio (dB/100m)

PSNEXT Power Sum Near End Crosstalk (db/100m)

PSACR Power Sum Attenuation to Crosstalk Ratio (dB/100m)

ACRF Attenuation to Crosstalk Ratio - Far End (dB/100m)

PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)

RL Return Loss (dB)

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL	
	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ	Std	Typ
1	2.0	1.9	65.3	83.1	63.3	81.2	62.3	80.8	60.3	78.9	63.8	84.4	60.8	82.4	20.0	33.0
4	4.1	3.7	56.3	73.4	52.2	69.8	53.3	71.3	49.2	67.6	51.8	73.3	48.8	71.4	23.0	30.6
8	5.8	5.2	51.8	69.0	46.0	63.9	48.8	67.0	43.0	61.8	45.7	67.4	42.7	65.5	24.5	31.5
10	6.5	5.8	50.3	67.2	43.8	61.4	47.3	65.1	40.8	59.3	43.8	65.4	40.8	63.5	25.0	32.4
16	8.2	7.4	47.2	64.1	39.0	56.8	44.2	62.0	36.0	54.7	39.7	61.3	36.7	59.4	25.0	31.8
20	9.3	8.2	45.8	62.6	36.5	54.4	42.8	60.5	33.5	52.2	37.8	59.4	34.8	57.4	25.0	33.0
25	10.4	9.2	44.3	60.9	33.9	51.6	41.3	58.8	30.9	49.6	35.8	57.6	32.8	55.5	24.3	33.1
31.25	11.7	10.3	42.9	59.6	31.2	49.2	39.9	57.4	28.2	47.1	33.9	55.6	30.9	53.5	23.6	33.4
62.5	17.0	14.7	38.4	54.4	21.4	39.8	35.4	52.4	18.4	37.7	27.9	49.5	24.9	47.4	21.5	32.9
100	22.0	18.6	35.3	51.0	13.3	32.4	32.3	48.9	10.3	30.2	23.8	45.5	20.8	43.3	20.1	29.9
155		23.4		46.9		23.5		45.1		21.7		41.3		39.3		28.0
200		26.7		45.1		18.4		43.2		16.5		39.1		37.0		26.0
250		29.9		44.8		14.9		42.7		12.8		37.1		35.1		25.1
300		32.9		43.0		10.1		40.9		8.0		35.6		33.4		25.0
350		35.7		41.6		5.9		39.7		3.9		34.1		31.8		25.6