

3297B-B Category 7 S/FTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1640 ft (500 m) length, reel


Product Classification

Portfolio	SYSTIMAX®
Product Type	Twisted pair cable
Regional Availability	EMEA

Standards And Qualifications

EN50575 CPR Cable EuroClass B2ca | s1 | d1 | a1

Cross Section Drawing



Construction Materials

Jacket Material	Low Smoke Zero Halogen (LSZH)
Conductor Material	Bare copper
Insulation Material	Polyolefin

Separator Material	Polyolefin
Shield (Braid) Material	Tinned copper
Shield (Tape) Material	Polyester/Aluminum shield

Dimensions

Cable Length	500 m 1640 ft
Cable Length Tolerance	±5%
Cable Weight	38.30 lb/kft
Diameter Over Jacket, nominal	7.391 mm 0.291 in
Jacket Thickness	0.635 mm 0.025 in

Electrical Performance

IL	Insertion Loss (dB/100m)
NEXT	Near End Crosstalk (dB/100m)
PSNEXT	Power Sum Near End Crosstalk (dB/100m)
ELFEXT	Equal-Level Far End Crosstalk (dB/100m)
PSELFEXT	Power Sum Equal-Level Far End Crosstalk (dB/100m)
RL	Return Loss (dB)

Freq (MHz)	IL	NEXT	PSNEXT	ELFEXT	PSELFEXT	RL
1	2.0	78.0	75.0	78.0	75.0	20.0
4	3.7	78.0	75.0	78.0	75.0	23.0
8	5.2	78.0	75.0	77.2	74.2	24.5
10	5.9	78.0	75.0	75.3	72.3	25.0
16	7.4	78.0	75.0	71.2	68.2	25.0
20	8.3	78.0	75.0	69.3	66.3	25.0
25	9.3	78.0	75.0	67.3	64.3	24.3
31.25	10.4	78.0	75.0	65.4	62.4	23.6
62.5	14.9	75.5	72.5	59.4	56.4	21.5
100	19.0	72.4	69.4	55.3	52.3	20.1
155	24.0	69.5	66.5	51.5	48.5	18.8
200	27.5	67.9	64.9	49.3	46.3	18.0
250	31.0	66.4	63.4	47.3	44.3	17.3
300	34.2	65.2	62.2	45.8	42.8	17.3
350	37.2	64.2	61.2	44.4	41.4	17.3
400	40.0	63.4	60.4	43.3	40.3	17.3
500	45.3	61.9	58.9	41.3	38.3	17.3
550	47.7	61.3	58.3	40.5	37.5	17.3
600	50.1	60.7	57.7	39.7	36.7	17.3
650	52.4	60.2	57.2	39.0	36.0	17.3

*Values above 600 MHz are for engineering purposes only.

Electrical Specifications

ANSI/TIA Category	7
dc Resistance Unbalance, maximum	2 %
dc Resistance, maximum	7.61 ohms/100 m
Mutual Capacitance	4.2 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	80 %
Operating Frequency, maximum	600 MHz
Operating Voltage, maximum	80 V
Transmission Standards	CENELEC EN 50288-4-1 ISO/IEC 11801 Class F

Note All electrical transmission tests include swept frequency measurements

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Smoke Test Method	IEC 61034-2
Acid Gas Test Method	EN 50267-2-3
Installation Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	S/FTP (shielded)
Packaging Type	Reel
Pairs, quantity	4
Cable Component Type	Horizontal
Jacket Color	White
Product Number	3297B-B
Conductor Gauge, singles	23 AWG
Conductor Type, singles	Solid
Conductors, quantity	8

Mechanical Specifications

Pulling Tension, maximum 11 kg | 25 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available

