

# 240PJF-BH-CR

1.0/2.3 DIN Female Bulkhead for CNT-240 braided cable

**OBSOLETE**

## Product Classification

<b>Brand</b>	CNT®
<b>Product Type</b>	Braided cable connector

## General Specifications

<b>Interface</b>	1.0-2.3 DIN Female
<b>Body Style</b>	Bulkhead

## Electrical Specifications

<b>Operating Frequency Band</b>	0 – 6000 MHz
<b>Average Power at Frequency</b>	260.0 W @ 900 MHz
<b>Cable Impedance</b>	50 ohm
<b>Connector Impedance</b>	50 ohm
<b>RF Operating Voltage, maximum (vrms)</b>	250.00 V
<b>dc Test Voltage</b>	1000 V
<b>Outer Contact Resistance, maximum</b>	2.50 mOhm
<b>Inner Contact Resistance, maximum</b>	4.00 mOhm
<b>Insulation Resistance, minimum</b>	1000 MOhm
<b>Peak Power, maximum</b>	1.25 kW
<b>Insertion Loss, typical</b>	0.05 dB

## Mechanical Specifications

<b>Outer Contact Attachment Method</b>	Crimp
<b>Inner Contact Attachment Method</b>	Solder
<b>Interface Durability</b>	500 cycles
<b>Interface Durability Method</b>	IEC 61169-29:9.5
<b>Connector Retention Tensile Force</b>	134 N   30 lbf
<b>Connector Retention Torque</b>	0.23 N-m   0.17 ft lb
<b>Insertion Force</b>	10.00 N   2.25 lbf
<b>Insertion Force Method</b>	IEC 61169-29:9.3.5
<b>Pressurizable</b>	No

## Dimensions

# 240PJF-BH-CR

---

<b>Nominal Size</b>	0.240 in
<b>Diameter</b>	47.23 mm   1.86 in
<b>Length</b>	22.35 mm   0.88 in
<b>Weight</b>	78.00 g   0.17 lb
<b>Width</b>	22.35 mm   0.88 in

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Storage Temperature</b>	-65 °C to +125 °C (-85 °F to +257 °F)
<b>Water Jetting Test Mating</b>	Mated
<b>Water Jetting Test Method</b>	IEC 60529:2001, IP65
<b>Mechanical Shock Test Method</b>	IEC 60068-2-27
<b>Climatic Sequence Test Method</b>	IEC 60068-1
<b>Damp Heat Steady State Test Method</b>	IEC 60068-2-3
<b>Thermal Shock Test Method</b>	IEC 60068-2-14
<b>Vibration Test Method</b>	IEC 60068-2-6
<b>Corrosion Test Method</b>	IEC 60068-2-11

## Standard Conditions

<b>Attenuation, Ambient Temperature</b>	20 °C   68 °F
<b>Average Power, Ambient Temperature</b>	40 °C   104 °F
<b>Average Power, Inner Conductor Temperature</b>	100 °C   212 °F

## Return Loss/VSWR

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
0–3000 MHz	1.09	27.30
3000–6000 MHz	1.22	20.10

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)



### \* Footnotes

# 240PJF-BH-CR

---

**Insertion Loss, typical**  $0.05\sqrt{\text{freq}}$  (GHz) (not applicable for elliptical waveguide)