

JACK, AMP-TWIST, UTP, C6A, E. IVORY



This product will be discontinued on: June 30, 2019

Replaced By

760241193
SL10G-E.IVY

NETCONNECT SL 110 Series Modular Jack, RJ45, category 6A, T568A/T568B, unshielded, no dust cover, electric ivory

Product Classification

| | |
|------------------------------|---|
| Portfolio | NETCONNECT® |
| Product Series | SL Series |
| Product Type | Modular jack |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America |

Dimensions

| | |
|---|---------------------|
| Compatible Cable Diameter, maximum | 9.00 mm 0.35 in |
| Compatible Insulated Conductor Diameter, maximum | 1.600 mm 0.063 in |
| Depth | 39.03 mm 1.54 in |
| Height | 21.50 mm 0.85 in |
| Width | 15.25 mm 0.60 in |

Electrical Specifications

| | |
|------------------------------|---|
| Safety Voltage Rating | 150 Vac |
| Transmission Standard | ANSI/TIA-568-C.2 ISO/IEC 11801 Class EA |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Safety Standard | cUL |

General Specifications

| | |
|-------------------------------------|-----------------------------------|
| Cable Type | Unshielded |
| Color | Electrical ivory |
| Includes | Strain relief cap |
| Mount Type | SL Series faceplates and panels |
| Package Quantity | 24 |
| Panel Cutout, recommended | 14.78 x 20.32 mm (0.58 x 0.80 in) |
| Panel Thickness, recommended | 1.60 mm |

Mechanical Specifications

| | |
|-------------------------------------|---------------------|
| Conductor Gauge, solid | 24–22 AWG |
| Conductor Gauge, stranded | 24 AWG |
| Conductor Type | Solid Stranded |
| Contact Base Material | Beryllium copper |
| Contact Plating Material | Gold |
| Contact Plating Thickness | 1.27 µm |
| Material Type | Polycarbonate |
| Outlet Feature | Inverted jack face |
| Outlet Type | Standard |
| Plug Insertion Life, minimum | 750 times |
| Termination Tool | SL Termination tool |
| Termination Type | IDC |
| Wiring | T568A T568B |

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification

