



## PICABOND® Connector, 1000 loose piece, green/amber

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for standard load coil, breakaway load coil and breakaway (add slack) splicing applications

## Product Classification

<b>Brand</b>	PICABOND®
<b>Product Type</b>	Splice
<b>Product Series</b>	PICABOND
<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America

## Electrical Specifications

**Safety Voltage Rating** 400 Vdc

## Environmental Specifications

**Environmental Space** Outdoor

**Operating Temperature** -40 °C to +60 °C (-40 °F to +140 °F)

## General Specifications

<b>Connector Color Code</b>	Green/Amber
<b>Connector Sealant</b>	Unfilled
<b>Connector Splicing Type</b>	Breakaway (add slack)   Breakaway Load Coil   Standard Load Coil
<b>Insulation Material</b>	Air Core PIC   Paper or Pulp
<b>Package Quantity</b>	1000
<b>Packaging Type</b>	Loose piece

## Mechanical Specifications

**Conductor Gauge, solid** 26–22 AWG

**Contact Base Material** Phosphor bronze

**Contact Plating Material** Tin

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

