

# 195PSCR-CR

---

SMC Male Right Angle for CNT-195 braided cable

## Product Classification

<b>Brand</b>	CNT®
<b>Product Type</b>	Braided cable connector

## General Specifications

<b>Interface</b>	SMC Male
<b>Body Style</b>	Right angle

## Electrical Specifications

<b>Operating Frequency Band</b>	0 – 6000 MHz
<b>Cable Impedance</b>	50 ohm
<b>Connector Impedance</b>	50 ohm
<b>RF Operating Voltage, maximum (vrms)</b>	335.00 V
<b>dc Test Voltage</b>	750 V
<b>Outer Contact Resistance, maximum</b>	2.50 mOhm
<b>Inner Contact Resistance, maximum</b>	5.00 mOhm
<b>Insulation Resistance, minimum</b>	5000 MOhm
<b>Average Power</b>	150.0 W @ 900 MHz
<b>Peak Power, maximum</b>	2.20 kW
<b>Insertion Loss, typical</b>	0.05 dB

## Mechanical Specifications

<b>Outer Contact Attachment Method</b>	Crimp
<b>Outer Contact Plating</b>	Gold
<b>Inner Contact Plating</b>	Gold
<b>Inner Contact Attachment Method</b>	Solder
<b>Interface Durability</b>	500 cycles
<b>Interface Durability Method</b>	IEC 61169-9:9.5
<b>Connector Retention Tensile Force</b>	134 N   30 lbf
<b>Connector Retention Torque</b>	0.17 N-m   0.13 ft lb
<b>Insertion Force</b>	10.00 N   2.25 lbf
<b>Insertion Force Method</b>	IEC 61169-9:9.3.5
<b>Pressurizable</b>	No
<b>Coupling Nut Proof Torque</b>	0.71 N-m   0.52 ft lb
<b>Coupling Nut Proof Torque Method</b>	IEC 61169-9:9.3.6
<b>Coupling Nut Retention Force</b>	150.00 N   33.72 lbf
<b>Coupling Nut Retention Force Method</b>	IEC 61169-9:9.3.11

# 195PSCR-CR

---

## Dimensions

<b>Nominal Size</b>	0.195 in
<b>Diameter</b>	7.90 mm   0.31 in
<b>Length</b>	26.80 mm   1.06 in
<b>Weight</b>	5.00 g   0.01 lb
<b>Width</b>	7.90 mm   0.31 in

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Storage Temperature</b>	-65 °C to +125 °C (-85 °F to +257 °F)
<b>Water Jetting Test Mating</b>	Mated
<b>Water Jetting Test Method</b>	IEC 60529:2001, IP65
<b>Mechanical Shock Test Method</b>	IEC 60068-2-27
<b>Climatic Sequence Test Method</b>	IEC 60068-1
<b>Damp Heat Steady State Test Method</b>	IEC 60068-2-3
<b>Thermal Shock Test Method</b>	IEC 60068-2-14
<b>Vibration Test Method</b>	IEC 60068-2-6
<b>Corrosion Test Method</b>	IEC 60068-2-11

## Standard Conditions

<b>Attenuation, Ambient Temperature</b>	20 °C   68 °F
<b>Average Power, Ambient Temperature</b>	40 °C   104 °F
<b>Average Power, Inner Conductor Temperature</b>	100 °C   212 °F

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2015  
China RoHS SJ/T 11364-2014

### Classification

Compliant by Exemption  
Designed, manufactured and/or distributed under this quality management system  
Above Maximum Concentration Value (MCV)



## \* Footnotes

**Insertion Loss, typical** 0.05v\*freq (GHz) (not applicable for elliptical waveguide)