


PICABOND® Connector, LOOSE PIECE, MINI, BLUE



- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for high count straight splicing applications

Product Classification

Brand	PICABOND®
Product Type	Splice
Product Series	PICABOND
Regional Availability	Australia/New Zealand EMEA Latin America North America

Electrical Specifications

Safety Voltage Rating 400 Vdc

Environmental Specifications

Environmental Space Outdoor
Operating Temperature -40 °C to +60 °C (-40 °F to +140 °F)

General Specifications

Connector Color Code Blue
Connector Sealant Unfilled
Connector Splicing Type High Count Straight
Insulation Material Air Core PIC | Paper or Pulp
Package Quantity 250
Packaging Type Loose piece

Mechanical Specifications

Conductor Gauge, solid 26–22 AWG
Contact Base Material Phosphor bronze
Contact Plating Material Tin

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

