

THIS DRAWING IS A CONTROLLED DOCUMENT

DWG NO
501258

PART NUMBER	CONNECTOR TYPE	REMARKS
501258-7	ST STYLE, NEXT GENERATION SC	INCLUDES MICROSCOPE AND EPOXY HEATCURE OVEN FOR USE WITH 110V POWER
501258-8 INTERNATIONAL KIT	ST STYLE, NEXT GENERATION SC	INCLUDES MICROSCOPE AND EPOXY HEATCURE OVEN FOR USE WITH 240V POWER
501258-9	ST STYLE, NEXT GENERATION SC	DOES NOT INCLUDE MICROSCOPE OR HEATCURE OVEN

△ 1 OVEN KITS INCLUDE THE FOLLOWING ITEMS:
 CABLE SUPPORT ROD
 CABLE SUPPORT BRACKET
 CURE OVEN POWER CORD
 THUMBSCREW
 THERMOMETER

OBSOLETE

OBSOLETE

OBSOLETE

OBSOLETE

1	1	1	-	-	-	-	-	-	905080-7	LABEL, NEXT GEN FC&SC	36
1	1	1	-	-	-	-	-	-	905080-4	LABEL, ST STYLE	34
1	1	1	-	-	-	-	-	-	905080-2	LABEL, AMP SC	33
-	1	1	-	-	-	-	-	-	1754767-1	MICROSCOPE W/10X OBJECTIVE	32
-	1	-	-	-	-	-	-	-	502134-2	HEAT CURE OVEN, 240V △1	31
-	-	1	-	-	-	-	-	-	502134-1	HEAT CURE OVEN, 110V △1	30
10	10	10	-	-	-	-	-	-	502656-1	CURING SLEEVE, AMP SC	29
6	6	6	-	-	-	-	-	-	502259-2	CURING SLEEVE, ST STYLE	27
1	1	1	-	-	-	-	-	-	503910-1	DIE SET, NEXT GEN FC&SC	26
1	1	1	-	-	-	-	-	-	58424-1	DIE SET, ST	25
1	1	1	-	-	-	-	-	-	1976850-1	HAND TOOL FRAME(BLACK)	24
10	10	10	-	-	-	-	-	-	502631-1	POLISH BUSHING, AMP SC	23
1	1	1	-	-	-	-	-	-	503304-2	POLISH BUSH,BEIGE,ST STYLE	21
-9	-8	-7	-6	-5	-4	-3	-2	-1	PART NUMBER	DESCRIPTION	ITEM NO.

1	1	1	-	-	-	-	-	-	503304-1	POLISH BUSH,BLACK,ST STYLE	20
1	1	1	-	-	-	-	-	-	503337-1	POLISH BUSH,METAL,ST STYLE	19
5	5	5	-	-	-	-	-	-	502748-2	POLISHING FILM, FINAL	18
20	20	20	-	-	-	-	-	-	228433-8	POLISHING FIM, 5um	17
20	20	20	-	-	-	-	-	-	228433-7	POLISHING FILM, 1um	16
20	20	20	-	-	-	-	-	-	228433-5	POLISHING FILM, 0.3um	15
3	3	3	-	-	-	-	-	-	501858-1	POLISHING PAD, GREEN	14
3	3	3	-	-	-	-	-	-	501523-1	POLISHING PAD, WHITE	13
1	1	1	-	-	-	-	-	-	501197-1	POLISHING PLATE	12
1	1	1	-	-	-	-	-	-	501818-1	CABLE PREP TEMPLATE KIT	11
4	4	4	-	-	-	-	-	-	982395-1	PARTS BOX, CRIMP DIES	10
6	6	6	-	-	-	-	-	-	501473-3	EPOXY APPLICATOR	9
15	15	15	-	-	-	-	-	-	502282-2	EPOXY DISH	8
14	14	14	-	-	-	-	-	-	501857-2	ALCOHOL WIPES	7
1	1	1	-	-	-	-	-	-	504064-1	SCRIBE TOOL	6
1	1	1	-	-	-	-	-	-	1278637-1	KEVLAR SHEARS	5
1	1	1	-	-	-	-	-	-	504024-3	FIBER STRIPPER, (.012)	4
1	1	1	-	-	-	-	-	-	504024-1	FIBER STRIPPER, (.008)	3
1	1	1	-	-	-	-	-	-	1754708-1	FIBER STRIP TOOL, COMB.	2
1	1	1	-	-	-	-	-	-	501208-3	CARRYING CASE	1
-9	-8	-7	-6	-5	-4	-3	-2	-1	PART NUMBER	DESCRIPTION	ITEM NO.

LOC
CE
DIST
00

BE	REBRANDING	16MAR2017		
BD	REV; MCO-40025261MCO	13OCT2015	HG	TE
BC	REVISED PER ECR 11-020518	24OCT2011	DLF	SB
LTR	REVISION RECORD	DATE	DWN	APVD

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ±.
 1 PLC ±.
 2 PLC ±.
 3 PLC ±.
 4 PLC ±.


ANGLES ±
SURFACE TEXTURE

DWN	B.BRIGGS	27JUL2005	MATERIAL	-	HEAT TREAT	-					
CHK	D.KIRSCH	27JUL2005	COMMSCOPE, INC.								
APVD	S.BUCHTER	27JUL2005									
NAME							PROFESSIONAL INSTALLERS TOOL KIT				
SCALE	1:2	SIZE	A2	DRAWING NO	501258	SHEET	1	OF	2	REV	BE


© 2016 COMMSCOPE, INC. CONFIDENTIAL
NOTICE: THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPRIETARY PROPERTY OF COMMSCOPE, INC. AND MAY BE USED ONLY FOR THE SPECIFIC PURPOSE AUTHORIZED IN WRITING BY COMMSCOPE, INC.

TOP SECTION

ITEMS 2, 5, 12 THRU 18 AND INSTRUCTION SHEETS
ARE LOCATED IN DIVIDER POUCH



BOTTOM SECTION



LOC	CE			
DIST	00			
LTR	REVISION RECORD	DATE	DWN	APVD
-	SEE SHEET 1	-	-	-

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		0 PLC	±
		1 PLC	±
		2 PLC	±
		3 PLC	±
		4 PLC	±
ANGLES ±		-	
SURFACE TEXTURE		√	

DWN	B.BRIGGS	27 JUL 2005	MATERIAL	-	HEAT TREAT	-					
CHK	D.KIRSCH	27 JUL 2005	COMMSCOPE, INC.								
APVD	S.BUCHTER	27 JUL 2005									
NAME							PROFESSIONAL INSTALLERS TOOL KIT				
SCALE	1:2	SIZE	A2	DRAWING NO	501258	SHEET	2	OF	2	REV	BE

© 2016 COMMSCOPE, INC. CONFIDENTIAL
NOTICE: THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPRIETARY PROPERTY OF
COMMSCOPE, INC. AND MAY BE USED ONLY FOR THE SPECIFIC PURPOSE AUTHORIZED IN WRITING BY COMMSCOPE, INC.