



SYSTIMAX 360™ iPatch® 1100 Angled Evolve Panel, 48 port without modules

Product Classification

| | |
|------------------------------|---|
| Portfolio | SYSTIMAX® |
| Brand | iPatch® SYSTIMAX 360™ |
| Product Type | RJ45 patch panel |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Dimensions

| | |
|--|----------------------|
| Depth | 266.70 mm 10.50 in |
| Diameter Over Dielectric, maximum | 1.168 mm 0.046 in |
| Diameter Over Dielectric, minimum | 0.762 mm 0.030 in |
| Height | 44.45 mm 1.75 in |
| Weight | 0.73 kg 1.60 lb |
| Width | 482.60 mm 19.00 in |

Electrical Specifications

| | |
|--|-------------------------------|
| ANSI/TIA Category | 6 6A |
| Current Rating at Temperature | 1.5 A @ 20 °C 1.5 A @ 68 °F |
| Dielectric Withstand Voltage, RMS, conductive surface | 1,500 Vac @ 60 Hz |
| Dielectric Withstand Voltage, RMS, contact-to-contact | 1,000 Vac @ 60 Hz |
| Insulation Resistance, minimum | 500 MOhm |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -5 °C to +50 °C (+23 °F to +122 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Safety Standard | ACMA CE cUL UL |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

General Specifications

| | |
|------------------------------|-----------------|
| Intelligence Type | iPatch® enabled |
| Total Ports, quantity | 48 |
| Cable Type | Unshielded |

| | |
|-------------------------|--|
| Color | Cool gray |
| Includes | Eight "A" labels Eight #12-24 mounting screws Forty-eight cable ties Instruction sheet Panel Two cable management bars |
| Package Quantity | 1 |
| Rack Units | 1.0 |

Mechanical Specifications

| | |
|---------------------------------------|---|
| Panel Style | Angled |
| Contact Plating Material | Precious metals |
| Material Type | Acrylonitrile butadiene styrene (ABS) Polycarbonate |
| Plug Insertion Life, minimum | 750 times |
| Plug Insertion Life, test plug | IEC 60603-7 compliant plug |
| Plug Retention Force, minimum | 30 lbf 133 N |
| Wiring | T568A T568B |

Regulatory Compliance/Certifications

| Agency | Classification |
|----------------------------------|--|
| RoHS 2011/65/EU ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

