



Middle of Pole Pico Concealment Enclosure for low power remote micro radio heads

- Intended to be used with remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

Product Classification

Product Type Metro cell site enclosure

Dimensions

Depth 304.8 mm | 12.0 in
Height 1016.0 mm | 40.0 in
Weight (loaded) 36.3 kg | 80.0 lb
Weight (unloaded) 18.1 kg | 40.0 lb
Width 401.3 mm | 15.8 in

General Specifications

Color Light Grey (RAL 7035)
Color Notes SSC-760236114xx1 - Light Grey | SSC-760236114xx2 - Green | SSC-760236114xx3 - Black | SSC-760236114xx4 - Brown
Color Options Black | Brown (RAL 8014) | Green (RAL 6005)
Finish Aluminum Chromate
Finish Concealment Covers Powder coated
Material Aluminum | Steel

Electrical Specifications

Power/Fiber Input Trade size knockouts at rear side

Antenna Specifications

Antennas Included None

Radio Specifications

Radio Compatibility, Ericsson (1) 4415/4426 Radio & (1) 2203/2205/2208 | (6) 2203/2205/2208 radios
Radio Compatibility, Nokia (1) Airscale Dual Band 160W + (1) AirScale micro radio | (1) DC Rectifier (Nokia FPAE OR Delta 1kw or 1.8kW) | SSC-760236114N2x | SSC-760236114N3x | Up to (4) AirScale micro radios

SSC-760236114 | Pico Radio Enclosure

Radios Included None

Mechanical Specifications

Mounting Options Wood poles | Tapered poles | Non-tapered poles

Environmental Specifications

Cooling Passive Cooling

Thermal Compliance GR-487

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

