

ATTEN-NMNF-10



Inline Attenuator, N-m/N-f, 10 dB

Product Classification

Product Type Coax attenuator

Electrical Specifications

Attenuation 10.0 dB
Attenuation Tolerance ± 0.5 dB
Impedance 50 ohm
Input Power, PEP, maximum 250 W
Input Power, RMS, maximum 2 W
Operating Frequency Band DC – 3000 MHz
Return Loss, minimum 20.00 dB

Mechanical Specifications

Connector Interface N Female | N Male
Dielectric Material PTFE
Inner Contact Plating Gold
Material Type, Body Brass
Outer Contact Plating Trimetal
Plating Nickel

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Dimensions

Diameter 16.0 mm | 0.6 in
Length 70.0 mm | 2.8 in
Weight 77.0 g | 0.2 lb

ATTEN-NMNF-10

Outline Drawing

