

# CT-8-TCPUSE-43-i6

8 dB, Tapper, 340–960/1710–2700 MHz



## Product Classification

**Product Type** Coaxial splitter

## General Specifications

**Device Type** Tapper  
**Interface** 4.3-10 Female  
**Color** Silver

## Electrical Specifications

**Operating Frequency Band** 1710 – 2700 MHz | 340 – 960 MHz  
**3rd Order IMD** -162.0 dBc  
**3rd Order IMD Test Method** Two +43 dBm carriers  
**Average Power, maximum** 300 W  
**Coupling** 8.0 dB  
**Coupling Tolerance** ±0.8 dB @ 1710–2700 MHz | ±0.8 dB @ 698–960 MHz | ±1.2 dB @ 340–698 MHz  
**Impedance** 50 ohm  
**Insertion Loss at Frequency Band** 1.1 dB @ 1710–2700 MHz | 1.1 dB @ 340–698 MHz | 1.1 dB @ 698–960 MHz  
**Peak Power, maximum** 3 kW  
**Reflected Power, maximum** 200 W  
**Return Loss, minimum** 19.1 dB  
**VSWR** 1.25:1

## Mechanical Specifications

**Coupling Nut Proof Torque** 7.00 N-m | 5.16 ft lb  
**Inner Contact Plating** Silver  
**Outer Contact Plating** Trimetal

## Environmental Specifications

**Application** Indoor/Outdoor  
**Ingress Protection Test Method** IEC 60529:2001, IP65  
**Operating Temperature** -35 °C to +85 °C (-31 °F to +185 °F)  
**Relative Humidity** Up to 100%

## Dimensions

<b>Height</b>	25.00 mm   0.98 in
<b>Length</b>	146.00 mm   5.75 in
<b>Width</b>	46.00 mm   1.81 in
<b>Net Weight</b>	250.00 g   0.55 lb

## Packed Dimensions

<b>Height</b>	40.0 mm   1.6 in
<b>Length</b>	180.0 mm   7.1 in
<b>Width</b>	90.0 mm   3.5 in
<b>Shipping Weight</b>	350.00 g   0.77 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

