

## 10 dB Low PIM Attenuator 555–2700 4.3-10 M-F



### Product Classification

**Product Type** Attenuator

### General Specifications

**Device Type** Attenuator  
**Interface** 4.3-10 Male  
**Color** Silver  
**Interface 2** 4.3-10 Female

### Electrical Specifications

**Operating Frequency Band** 555 – 2700 MHz  
**3rd Order IMD** -162.0 dBc  
**3rd Order IMD Test Method** Two +43 dBm carriers  
**Attenuation** 10.0 dB  
**Attenuation Tolerance**  $\pm 1.0$  dB @ 698–2700 MHz |  $\pm 2.0$  dB @ 555–698 MHz  
**Average Power, maximum** 100 W  
**Impedance** 50 ohm  
**Return Loss, minimum** 19.0 dB  
**VSWR** 1.25:1

### Mechanical Specifications

**Inner Contact Plating** Silver  
**Outer Contact Plating** Trimetal

### Environmental Specifications

**Application** Indoor/Outdoor  
**Ingress Protection Test Method** IEC 60529:2001, IP65  
**Operating Temperature** -25 °C to +50 °C (-13 °F to +122 °F)  
**Relative Humidity** Up to 100%

### Dimensions

# AT-10-43-MFi6

---

<b>Height</b>	76.00 mm   2.99 in
<b>Length</b>	266.00 mm   10.47 in
<b>Width</b>	130.00 mm   5.12 in
<b>Net Weight</b>	2.80 kg   6.17 lb

## Packed Dimensions

<b>Height</b>	150.0 mm   5.9 in
<b>Length</b>	370.0 mm   14.6 in
<b>Width</b>	225.0 mm   8.9 in
<b>Shipping Weight</b>	3.37 kg   7.43 lb

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

