



OCC1D compact DWDM, 8 channels + upgrade port, single demux, 1561.42 nm starting wavelength, 0.9 mm cable, ruggedized housing

Product Classification

Product Type	DWDM component
Product Series	OCC1D
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Distribution Type	8-channel DWDM
Interface, input	Stub tail
Interface, output	Stub tail
Application	For use in FOSC closures
Circuits, quantity	1
Functionality	Demultiplexing
Multiplexers, quantity	1
Package, quantity	1
Port Type, optional	Upgrade port
Technology Type	Thin film filter (TFF)

Dimensions

Depth	3.97 mm 0.16 in
Height	9.14 mm 0.36 in
Pigtail Diameter	0.90 mm 0.04 in
Pigtail length, input	1.00 m 3.28 ft
Pigtail length, output	1.00 m 3.28 ft
Width	60.96 mm 2.40 in

Mechanical Specifications

Device Type	Component, rectangular
--------------------	------------------------

Optical Specifications

Starting Wavelength 1561.42 nm
Channel Spacing 100 GHz

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

